
STANDARD CABLE CONNECTOR ASSEMBLY

FOR SIL 3 SERIES OF ENCODERS



Pinout Designations

Color	Pin	Function
Black	1	0V
Red	2	+Vdc
Yellow	3	А
Blue	4	В
Orange	5	Z
White/Yellow	6	A/
White/Blue	7	B/
White/Orange	8	Z/

Sensata

Technologies

Part Number	Model Number	Description (cable length, material, connector)	Compatibility
RAL-020-001	9416/076-8230/020-G6-020	2 m, PVC, for G6 Connection (M23)	DSK5H, DSK5HKB, DSU9, DSM9, DSO5, DSM5
RAL-030-001	9416/076-8230/020-G6-030	3 m, PVC, for G6 Connection (M23)	DSK5H, DSK5HKB, DSU9, DSM9, DSO5, DSM5
RAL-050-001	9416/076-8230/020-G6-050	5 m, PVC, for G6 Connection (M23)	DSK5H, DSK5HKB, DSU9, DSM9, DSO5, DSM5
RAL-100-001	9416/076-8230/020-G6-100	10 m, PVC, for G6 Connection (M23)	DSK5H, DSK5HKB, DSU9, DSM9, DSO5, DSM5
RAL-150-001	9416/076-8230/020-G6-150	15 m, PVC, for G6 Connection (M23)	DSK5H, DSK5HKB, DSU9, DSM9, DSO5, DSM5
RAL-020-012	9416/055-8230/050-G8-020	2 m, PUR, for G8 Connection (M23)	DSK5H, DSK5HKB
RAL-050-020	9416/055-8230/050-G8-050	5 m, PUR, for G8 Connection (M23)	DSK5H, DSK5HKB
RAL-100-028	9416/055-8230/050-G8-100	10 m, PUR, for G8 Connection (M23)	DSK5H, DSK5HKB
RAL-020-039	8230/369-GM-020	2 m, PUR, overmolded for M12 (GM) Connection	DSK5H, DSK5HKB, DSU9, DSM9, DSO5, DSM5
RAL-050-052	8230/370-GM-050	5 m, PUR, overmolded for M12 (GM) Connection	DSK5H, DSK5HKB, DSU9, DSM9, DSO5, DSM5
RAL-100-050	8230/371-GM-100	10 m, PUR, overmolded for M12 (GM) Connection	DSK5H, DSK5HKB, DSU9, DSM9, DSO5, DSM5

This cable assembly has been tested and approved for use with the Sensata | BEI Sensors series of functional safety encoders. Do not substitute any other cable assembly without factory consultation.

Page 1

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DATA SHEETS ON WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS.

All products are sold subject to Sensata's terms and conditions of sale supplied at <u>www.sensata.com</u> SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

CONTACT US

 Aniericas

 +1 (800) 350 2727 – Option 1

 sales.beisensors@sensata.com

 Europe, Middle East & Africa

 +33 (3) 88 20 8080

 position-info.eu@sensata.com

 Asia Pacific

 sales.isasia@list.sensata.com

 China +86 (21) 2306 1500

 Japan +81 (45) 277 7117

 Korea +82 (31) 601 2004

 India +91 (80) 67920890

 Rest of Asia +886 (2) 27602006

 ext 2808