





Applications

- $\cdot\,\,$ Reading of ID and member cards
- · E-Ticketing
- · Payment, POS System, Loyalty
- · Retail / Libraries
- · Identification / Access

Features

- · Multi-read UHF
- · Integrated antenna
- $\cdot \ \ \mathsf{SW} \ \mathsf{programmable} \ \mathsf{power}$
- · Supports ETSI & FCC band
- · Power over USB
- · SDK included
- · Optional HID version

RFID Options

· UHF (EPC C1 GEN2 / ISO18000-6C)

Pen Stick Reader EVO is a sleek and compact RFID reader with integrated, linear polarized antenna. Equipped with USB interface as standard, it is also available with Human Interface Device (HID).

This UHF Version supports ISO Standard 18000-6C EPC Class 1 Generation 2 transponders, as well as global UHF frequencies ETSI (865 - 868 MHz) and FCC (902 - 928 MHz).

EVO Stick Reader UHF allows reading ranges of up to 30 centimeters, depending on tag type and orientation.* Max. power output of 100mW (+20dBm) can be regulated via software in 1dB steps.

The EVO UHF is a versatile read and write device for various applications and work sites. A Software Development Kit for all Windows operating systems is available for download.

Technical Data

Electrical Specific	lectrical Specifications	
Power Supply	USB	
Current Consumption	up to 350 mA (High Powered Port needed)	
Operating Frequency	865–868 MHz (ETCI) 902–928 MHz (FCC) 916– 923.4 MHz (Japan)	
Max. Power	max 100 mW (+20 dBm) software programmable in 1dB steps	
Antenna	integrated, linear polarised	
Reader IC	AMS AS3992	
RF TX Speed	up to 640 kHz Link Frequency	
Interfaces	USB VCP, HID**	
HID Output Format	EPC only, hexadecimal, lowercase HID Output of EPC Memory of UHF Tags will be displayed.	
Connector	USB Type A plug	

Mechanical Specifications	
Dimensions	83.5 × 36 × 11.2 mm
Material	ABS (Acrylonitrile butadiene styrene)
Protection Class	IP40
Housing Colour	Light grey + dark grey
Weight	20 g

Environmental Conditions		
Operating Temperature	-10°C +50°C	
Storage Temperature	-20°C +70°C	
Humidity	up to 95%, non condensing	
MTBF	200'000 h	

Supported Standards/Tags

Standard ISO 18000-6C (EPC Class 1 Generation 2) E.g.: Alien Higgs 2/3/4, Impinj Monza, NXP UCODE, etc.

Applicable Standards	
EMC	EN 301489-1:2012-04 (v1.9.21) EN 301489-3:2013-12 (V1.6.1)
Radio Regulation	EN 300330-1:2015-08 (V1.8.1) EN 300330-2:2015-08 (V1.6.1)
Safety	EN 60950-1:2014-08 EN 62369-1:2010-03 EN 50364:2010-11
RoHS	EC Guideline 2011/65/EU
Certificates	FCC, CE

SDK Information	
Supported OS	Windows 7, 8, 8.1, 10
Supported Languages	C++, C#, .net, Java, binary command protocol
USB Driver OS	Windows NT based Windows 10 certified Linux (built-in)
Demo Software	Windows
Engineering Mode	License can be acquired separately

^{*} Reading distance depends on tag type and orientation.
** Human Interface Device

Order Codes

Version	Order Code
Stick Reader EVO UHF	R-STICK-EVO-UHF
Stick Reader EVO UHF HID	R-STICK-EVO-UHF-HID

iDTRONIC GmbH Ludwig-Reichling-Straße 4 67059 Ludwigshafen GERMANY

Phone +49 (0) 621 66 90 09 4-0 Fax +49 (0) 621 66 90 09 4-9 E-Mail: info@idtronic-rfid.com Web: idtronic-rfid.com