







Product Data Sheet RL90-18/06

RL90-18/06

INDEX

1	Ger	neral	3
2	Med	chanics	3
	2.1 2.2	General Connections	
3	Оре	erating Data	5
	3.1 3.2 3.3 3.4	ELECTRICAL OPERATING DATA ELECTRICAL FEATURES AERODYNAMICS SOUND DATA	6 6
4		vironment	
	4.1 4.2	GENERAL	7 7
5	Safe	ety	
	5.1 5.2	ELECTRICAL SAFETY APPROVAL TESTS	8 8
6	Reli	iability	
	6.1	GENERAL	8



1 General

Fan type	Blower
Rotating direction looking at rotor	Clockwise
Airflow direction	Air in axially, Air out radially
Bearing system	Ball bearing
Mounting position - shaft	Any
Balancing grade	2,5

2 Mechanics

2.1 General


Width	121,0 mm	
Height	121,0 mm	
Depth	37,0 mm	
Diameter	0,0 mm	
Mass	0,680 kg	
Housing material	Plastic	
Impeller material	Plastic	
Max. torque when mounted across both mounting	Wire outlet corner: 280 Ncm	
flanges	Remaining corners: 280 Ncm	
Screw size	ISO 4762 - M4 degreased, without an additional	
	brace and without washer	



01/31/2019 page 3 of 9

2.2 Connections

Electrical connection	Wires	
Lead wire length	L = 310,0 mm	
Tolerance	+- 10,0 mm	
Tube length	See drawing	
Tolerance		
Wire size (AWG)	22	
Insulation diameter	1,09 mm	
Plug	See drawing	
Contact	See drawing	



	Color	Operation
1	blue	L
2	blue	N



01/31/2019 page 4 of 9

3 Operating Data

3.1 Electrical Operating Data

Measurement Normal air density = 1,2 kg/m3; Temperature 23℃ +/- 3℃; Motor axis horizontal; warm-up

conditions: time before measuring 5 minutes (unless otherwise specified).

In the intake and outlet area should not be any solid obstruction within 0,5 m.

 $\Delta p = 0$: corresp. to free air flow (see chapter aerodynamics)

I: corresp. to RMS line current


Features	Condition	Symbol	Values	
Frequency	$\Delta p = 0$	f	50 Hz	60 Hz
Nominal voltage	$\Delta p = 0$	U _N	115 V +- 10 %	115 V +- 10 %
Tolerance	·			
Power consumption			21 W	21 W
Tolerance	$\Delta p = 0$	Р	+ 5 % - 10 %	+ 5 % - 10 %
Speed			2.450 1/min	2.550 1/min
Tolerance	$\Delta p = 0$	n	+- 3 %	+- 3 %



01/31/2019 page 5 of 9

3.2 Electrical Features

Locked rotor protection	Impedance
Locked rotor current at	



3.3 Aerodynamics

Measurement conditions:

Measured with a double chamber intake rig acc. to DIN EN ISO 5801.

Normal air density = 1,2 kg/m3; Temperature 23° +/ - 3° ;

In the intake and outlet area should not be any solid obstruction within 0,5 m. Motor shaft

horizontal.

The information is only valid under the specified test conditions and may be changed by the installation conditions. If there are deviations from the standard test conditions, the

characteristic values must be checked under the installed conditions.

a.) Operation condition:

2.450 1/min at free air flow Frequency: 50 Hz

Max. free-air flow ($\Delta p = 0 / \dot{V} = max.$)	35,0 m3/h
Max. static pressure ($\Delta p = \text{max.} / \dot{V} = 0$)	90 Pa

b.) Operation condition:

2.550 1/min at free air flow Frequency: 60 Hz

Max. free-air flow ($\Delta p = 0 / \dot{V} = max.$)	37,0 m3/h
Max. static pressure ($\Delta p = \text{max.} / \dot{V} = 0$)	130 Pa



01/31/2019 page 6 of 9

3.4 Sound Data

Measurement

Sound pressure level: 1 meter distance between microphone and the air intake.

conditions:

Sound power level: Acc. to DIN 45635 part 38 (ISO 10302) Sound power level: Acc. to DIN

45635 part 38 (ISO 10302)

Measured in a semianchoic chamber with a background noise level of Lp(A) < 5 dB(A)

For further measurement conditions see chapter aerodynamics.

a.) Operation condition:

2.450 1/min at free air flow Frequency: 50 Hz

Optimal operating point	6,0 m3/h @ 76 Pa	
Sound power level at the optimal operating point	5,4 bel(A)	
Sound pressure level at free air flow, measured in rubber bands		

b.) Operation condition:

2.550 1/min at free air flow Frequency: 60 Hz

Optimal operating point	9,0 m3/h @ 107 Pa	
Sound power level at the optimal operating point	5,8 bel(A)	
Sound pressure level at free air flow, measured in rubber bands		

4 Environment

4.1 General

Min. permitted ambient temperature TU min.	-30 ℃ / 50 Hz -30 ℃ / 60 Hz	
Max. permitted ambient temperature TU max.	70 ℃ / 50 Hz 85 ℃ / 60 Hz	
Min. permitted storage temperature TL min.	-40 ℃	
Max. permitted storage temperature TL max.	85 ℃	

4.2 Climatic Requirements*)

Humidity requirements	humid heat, constant; according to DIN EN 60068-2-	
	78, 14 days	
Water exposure	None	
Dust requirements	None	
Salt fog requirements	None	

Permitted application area:

The product is intended for use in sheltered rooms with controlled temperature and controlled humidity. Directly exposure to water must be avoided.

Pollution degree 1 (according DIN EN 60664-1)

There is either no pollution or it occurs only dry, non-conductive pollution. The pollution has no negative impact.



01/31/2019 page 7 of 9

5 Safety

5.1 **Electrical Safety**

Dielectric strength	
DIN EN 60950 (VDE 0805) and DIN EN 60335 (VDE	
0700)	
A.) Type test	1000 VAC / 1 Min.
Measuring conditions: After 48h of storage at 95%	
R.H. and 25℃.	
No arcing or breakdown is allowed!	
All connections together to ground.	
B.) Routine test	1500 VAC / 1 Sec.
Measuring conditions: At indoor climate.	
No arcing or breakdown is allowed!	
All connections together to ground.	
Isolation resistance	RI > 50 MOhm
Measuring conditions: After 48h of storage at 95%	
R.H. and 25℃ measured with U=500 VDC for 1 min.	
Clearance / creepage distance	2,0 mm / 1,1 mm
Protection class	

5.2 **Approval Tests**

CE	EC Declaration of Conformity	Yes
EAC	Eurasian Conformity	Yes
UL	Underwriters Laboratories	Yes / UL507, Electric Fans
VDE	Association for Electrical, Electronic and	Yes / Approval acc. to EN 60950 (VDE 0805) - Information
	Information Technologies	technology equipment
CSA	Canadian Standards Association	Yes / C22.2 No. 113 Fans and Ventilators
CCC	China Compulsory Certification	Yes / GB 12350 Safety Requirements for small Power Motors

The approval tests are observed to: U approval max.: 115 V / f: 60 Hz @ TU approval max.: 75 $^{\circ}\mathrm{C}$

6 Reliability

6.1 General

If the expectancy (1.10 at 111 = 40.4).	37.500 h / 50 Hz 37.500 h / 60 Hz	
Life expectancy L10 at TU max.	20.000 h / 50 Hz 15.000 h / 60 Hz	



01/31/2019 page 8 of 9

