Features

Regulated Converter

- Universal input 85-305VAC
- 3W PCB mount package
- <75mW No load power consumption
- Ultra low profile, compact size
- -40°C to +85°C operating temperature
- Continuous SCP, OCP, OVP
- EN60335, IEC/EN/UL60950 CE certified

Description


The RACO3-GA series are low cost AC/DC power supplies, ideal for PCB mounted, compact, board level industrial applications. They feature universal AC input voltage range, regulated and short-circuit -proof isolated DC outputs, low standby power consumption and -40°C to +85°C operating temperature range. The RACO3-GA have a built-in Class A / FCC Part 15 EMC filter, are certified to IEC/EN/UL60950-1 and EN60335 and are pending to IEC/EN/UL62368 and EN61558 safety standards and come with a three year warranty.

Selection Guide						
Part Number	Input Voltage Range [VAC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ ⁽¹⁾ [%]	Max. Capacitive Load ⁽²⁾ [μF]	
RAC03-3.3SGA	85-305	3.3	910	70	2000	
RAC03-05SGA	85-305	5	600	72	1500	
RAC03-12SGA	85-305	12	250	78	500	
RAC03-15SGA	85-305	15	200	78	200	
RAC03-24SGA	85-305	24	130	80	150	
On Request						
RAC03-09SGA	85-305	9	330	77	1000	

Notes:

Note1: Efficiency is tested at 230VAC and full load at +25°C ambient Note2: Max. Cap. Load is tested at nominal input and full resisitive load

Model Numbering



Ordering Examples:

RAC03-12SGA 12Vout Single Output EMC Class A



RAC03-GA

3 Watt Single Output EMC Class A



















UL60950-1 certified IEC/EN60950-1 certified UL62368-1 certified IEC/EN62368-1 certified EN61558-1 certified EN61558-2-16 certified EN60335-1 certified CB Report



Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS						
Parameter	Condition		Min.	Тур.	Max.	
Internal Input Filter						Pi-type
Input Voltage Range (3,4)	nom.	Vin = 230VDC		85VAC 120VDC		305VAC 430VDC
Input Current		115VAC 230VAC			70mA 45mA	
Inrush Current	cold start at 25°C	115VAC				10A 20A
No load Power Consumption						75mW
Input Frequency Range		AC Input		45Hz		65Hz
Minimum Load				0%		
Power Factor	115VAC 230VAC			0.53 0.41		
Start-up Time	115VAC, 230VAC			30ms	1s	
Hold-up time	115VAC 230VAC			5ms 40ms		
Internal Operating Frequency	100% ld	100% load at nominal Vin			65kHz	
		0°C to 85 °C	3.3Vout 5Vout 12Vout 15Vout 24Vout			100mVp-p 100mVp-p 150mVp-p 200mVp-p 240mVp-p
Output Ripple and Noise (5)	20MHz BW	-30 °C to 0 °C	3.3Vout 5Vout 12Vout 15Vout 24Vout			200mVp-p 200mVp-p 250mVp-p 300mVp-p 300mVp-p


Notes:


Note3: The products were submitted for safety files at AC-Input operation

Note4: Refer to "Line Derating"

Note5: Measurements are made with a 12" twisted pair-wire with a 0.1µF and 10µF parallel capacitor across output (low ESR)

Efficiency vs. Load









Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

REGULATIONS				
Parameter	Condition	Value		
Output Accuracy		±2.5% max.		
Line Regulation	low line to high line	±0.5% max.		
Load Regulation	10% to 100% load	0.5% max.		





PROTECTIONS				
Parameter	Т	уре		Value
Input Fuse (6)	int	ternal		T1A, 300V
Short Circuit Protection (SCP)	below	100mΩ	long-term mode, auto recover	
	3.	3Vout	3.8V - 4.9V	
	5	Vout	5.3V - 6.8V	
Over Voltage Protection (OVP)	12	2Vout	12.6V - 16.2V	hiccup mode, auto recovery
	15	5Vout	15.75V - 20.3V	
	24	4Vout	25.2V - 32.4V	
Over Voltage Category				OVCII
	3.	3.3Vout		
	5	Vout	0.91A - 2.2A	
Over Current Protection (OCP)	12	12Vout		hiccup mode, auto recovery
	15	15Vout		
	24	24Vout		
Class of Equipment				Class II
Isolation Voltage (7)	I/P to O/P	I/P to O/P rated for 1 minute		3kVAC/10mA
Isolation Resistance				10M Ω min.
Insulation Grade				reinforced
Leakage Current	277VAC, 50Hz		0.1mA max.	


Notes:

Note6: Refer to local wiring regulations if input over-current protection is also required

Note7: For repeat Hi-Pot testing, reduce the time and/or the test voltage

Note8: For operation ≥230VAC, an external MOV is recommended. The Varistor should comply with IEC61051-2. eg. EPCOS S14 series

Protection Circuit






Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)


ENVIRONMENTAL				
Parameter	Condition		Value	
0 11 7	@ natural convection 0.1m/s	full load	-40°C to +70°C	
Operating Temperature Range	@ Hatural convection 0.111/5	refer to derating graph	-40°C to +85°C	
Maximum Case Temperature			+100°C	
Temperature Coefficient			0.03%/K	
Operating Altitude			3000m	
Operating Humidity	non-condensing		5% - 95% RH	
Pollution Degree			PD2	
Shock			20G/11ms pulse, 3 times at each x, y, z axes	
Vibration			10-150Hz, 2G 10min./1cycle, period 60min.	
VIDIATION			along x,y,z axes for 6 cycles	
MTBF	according to MIL-HDBK-217F, G.B.	+25°C	100 x 10 ³ hours	
IVIIDF	according to MIL-HDBR-2171, G.B.	+70°C	17 x 10 ³ hours	

Derating Graph

(@ Chamber and natural convection 0.1m/s)



Line Derating



SAFETY AND CERTIFICATIONS					
Certificate Type (Safety)	Report / File Number	Standard			
Information Technology Equipment, General Requirements for Safety		UL60950-1, 2nd Edition, 2014			
Information recliniology Equipment, denotal nequirements for earliety	E196683-A4-UL	CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014			
Audio/video, information and communication technology equipment. Safety requirements	L190003-A4-0L	UL62368-1, 2nd Edition			
Addiovided, information and communication technology equipment. Safety requirements		CAN/CSA C22.2 No 62368-1-14			
Information Technology Equipment, General Requirements for Safety	0417001040 001	EN60950-1: 2006 + A2:2013			
Information Technology Equipment, General Requirements for Safety (CB)	SA1703184S 001	IEC60950-1:2005, 2nd Edition + A2:2013			
Audio/video, information and communication technology equipment. Safety requirements	4787985921-	EN62368-1: 2014			
Audio/video, information and communication technology equipment. Safety requirements (CB)	20171025-CB	IEC62368-1:2014, 2nd Edition			
Household and similar electrical appliances – Safety – Part 1: General requirements	011 000771 000	EN60335-1:2012+A12:2017			
Household and similar electrical appliances – Safety – Part 1: General requirements (CB)		IEC60335-1:2010, 5th Edition + A1:2013			
Household and similar electrical appliances – Safety – Part 1: General requirements		EN60335-1:2012+A11:2014			
Measurement methods for electromagnetic fields of household appliances and similar apparatus with regard to human exposure	SA1703184L 01001	EN62233:2008			



Series


Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Certificate Type (Safety)	Report / File Number	Standard
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V	SA 1703184L 02001 -	EN61558-1: 2005 + A1:2009
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V Part 2: Particular requirements	SA 1703104L 02001	EN61558-2-16: 2009 + A1:2013
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 $\rm V$	211-600770-000	EN61558-1: 2005 + A1:2009
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V Part 2: Particular requirements	211-000770-000	EN61558-2-16: 2009 + A1:2013
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V (CB)	- 211-600770-000 -	IEC61558-1:2005, 2nd Edition + A1:2009
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V Part 2: Particular requirements (CB)	211-000770-000	IEC61558-2-16:2009, 1st Edition + A1:2013
EAC	RU-AT.03.67361	TP TC 004/020, 2011
RoHS 2+		RoHS 2011/65/EU + AM2015/863
EMC Compliance	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment – Emission Requirements (9)		EN55032: 2015, Class A
Information technology equipment - Immunity characteristics - Limits and methods of measurement	EA1703184E 01001	EN55024:2010 + A1:2015
Limitations on the amount of electromagnetic interference allowed from digital and electronic devices	EA1703184F 01001	47 CFR FCC Part 15 Subpart B: 2016
ESD Electrostatic discharge immunity test	Air ±8kV, Contact ±4kV	EN61000-4-2: 2009, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	3V/m	EN61000-4-3: 2006 + A2, 2010, Criteria A
Fast Transient and Burst Immunity	AC Port ±1kV	EN61000-4-4: 2012, Criteria A
Surge Immunity	AC Port L-N ±1kV	EN61000-4-5: 2014, Criteria B
Immunity to conducted disturbances, induced by radio-frequency fields	AC Power Port 3V	EN61000-4-6: 2014, Criteria A
	Voltage Dips >95%	EN61000-4-11: 2004, Criteria A
	1 7 1	
Voltage Dips and Interruption	Voltage Dips 30% Interruptions >95%	EN61000-4-11: 2004, Criteria A EN61000-4-11: 2004, Criteria C

Notes:

Note9: If output is connected to GND, please contact RECOM tech support for advice

EMC Filtering according to EN55014-1 / EN55032 Class B Compliance



CY1, CY2	CX1	
1nF, 2kV	100nF, 2kV	

DIMENSION AND PHYSICAL CHARACTERISTICS


Parameter	Туре	Value
Material	case	black plastic, (UL94 V-0)
Material	PCB	FR4, (UL94 V-0)
Dimension (LxWxH)		37.0 x 24.0 x 15.0mm
Weight		20g typ.

continued on next page



Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)



PACKAGING INFORMATION				
Parameter	Туре	Value		
Packaging Dimension (LxWxH)	tube	505.0 x 39.7 x 23.2mm		
Packaging Quantity		20pcs		
Storage Temperature Range		-40°C to +100°C		
Storage Humidity	non-condensing	5% -95% RH max.		

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.