Features

- Universal input 85-305VAC
- 4W PCB mount package
- <75mW No load power consumption
- Regulated Converter
- Ultra low profile, compact size
 -40°C to +85°C Operating temperature
- Continuous SCP, OCP, OVP
 - IEC/EN/UL60950 & CE certified, EN55032 Class B

Description

The RAC04-GB series are low cost AC/DC power supplies, ideal for PCB mounted, compact, board level industrial applications. They feature universal AC input voltage range, regulated and short-circuit-proof isolated DC outputs, low standby power consumption and -40°C to +85°C operating temperature range. The RAC04-GB have a built-in Class B / FCC Part 15 EMC filter, are certified to IEC/EN/UL60950-1 and are pending to IEC/EN/UL62368 and EN61558 safety standards and come with a three year warranty.

Selection Guide

Part Number	Input Voltage Range [VAC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ ⁽¹⁾ [%]	Max. Capacitive Load ⁽²⁾ [µF]
RAC04-3.3SGB	85-305	3.3	1210	70	2000
RAC04-05SGB	85-305	5	800	72	1500
RAC04-09SGB	85-305	9	440	77	1000
RAC04-12SGB	85-305	12	330	78	500
RAC04-15SGB	85-305	15	270	78	200
RAC04-24SGB	85-305	24	170	80	150

Notes:

Note1: Efficiency is tested at 230VAC and full load at +25°C ambient Note2: Max. Cap. Load is tested at nominal input and full resistive load



RAC04-GB








UL60950-1 certified IEC/EN60950-1 certified UL62368-1 pending IEC/EN62368-1 certified EN61558-1 certified EN61558-2-16 certified CB report

Model Numbering



Ordering Examples: RAC04-12SGB

12Vout Single Output

EMC Class B

RAC04-GB

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

So	ri		C
Se		e	3

Parameter	Condition		Min.	Тур.	Max.	
Internal Input Filter						Pi-type
Input Voltage Range (3,4)				85VAC 120VDC		305VAC 430VDC
Input Current	115VAC 230VAC			85mA 55mA		
Inrush Current	cold start at 25°C	cold start at 25°C 115VAC 230VAC				10A 20A
No load Power Consumption						75mW
Input Frequency Range		AC Input		45Hz		65Hz
Minimum Load				0%		
Power Factor		115VAC 230VAC			0.55 0.42	
Start-up Time	1-	115VAC, 230VAC			30ms	1s
Hold-up time		115VAC 230VAC			10ms 40ms	
Internal Operating Frequency	100%	load at nominal Vin			65kHz	
Outout Directo and Maior (5)		0°C to 85 °C	3.3Vout 5Vout 9Vout 12Vout 15Vout 24Vout			100mVp-p 100mVp-p 120mVp-p 150mVp-p 200mVp-p 240mVp-p
Output Ripple and Noise (5)	20MHz BW	Hz BW -30 °C to 0 °C -30 °C to 0 °C				200mVp-p 200mVp-p 250mVp-p 250mVp-p 300mVp-p 300mVp-p


Notes:

Note3: The products were submitted for safety files at AC-Input operation

Note4: Refer to line derating graph on page PA-4

Note5: Measurements are made with a 12" twisted pair-wire with a 0.1µF and 10µF parallel capacitor across output (low ESR)


Efficiency vs. Load




RAC04-GB Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Parameter	Condition	Value
Output Accuracy		±2.5% max
Line Regulation	low line to high line	±0.5% max
Load Regulation	10% to 100% load	0.5% max.





Parameter	1	Туре		Value	
Input Fuse ⁽⁶⁾	in	ternal	T1A slow blow type, 3		
Short Circuit Protection (SCP)	below	below 100mΩ		long-term mode, auto recovery	
	3.	3Vout	3.8V - 4.9V		
	5	Vout	5.3V - 6.8V		
Quer Veltage Distantion (QVD)	g	Vout	10.3V - 12.2V	hiccup mode, auto recovery	
Over Voltage Protection (OVP)	12	2Vout	12.6V - 16.2V		
	1	5Vout	15.75V - 20.3V	V	
	24	4Vout	25.2V - 32.4V		
Over Voltage Category				OVCII	
	3.	3Vout	1.41A - 3A	hiccup mode, auto recovery	
	5	Vout	0.91A - 2.2A		
	g	Vout	0.49A - 1.25A		
Over Current Protection (OCP)	12	2Vout	0.37A - 0.95A		
	1!	15Vout			
	24	4Vout	0.19A -0.45A		
Class of Equipment				Class II	
Isolation Voltage (7)	I/P to O/P	rated for 1 minute	3kVAC/10		
Isolation Resistance			10MΩ m		
Isolation Capacitance			800pF min. / 1200pF ma		
Insulation Grade				reinforced	
Leakage Current	277VAC, 50Hz		0.1mA max.		

continued on next page


RAC04-GB Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Notes:


- Note6: Refer to local wiring regulations if input over-current protection is also required
- Note7: For repeat Hi-Pot testing, reduce the time and/or the test voltage
- Note8: For operation ≥230VAC, an external MOV is recommended. The Varistor should comply with IEC61051-2. eg. EPCOS S14 series

Protection Circuit



ENVIRONMENTAL				
Parameter	Condition	Condition		Value
		fu	ll load	-40°C to + 70°C
Operating Temperature Range	@ natural convection 0.1m/s	refer to d	erating graph	-40°C to + 85°C
Maximum Case Temperature				+100°C
Temperature Coefficient				0.03%/K
Operating Altitude				3000m
Operating Humidity	non-condens	ing		5% - 95% RH
Pollution Degree				PD2
Shock				20G/11ms pulse, 3 times at each x, y, z axes
Vibration				10-150Hz, 2G 10min./1cycle, period 60min.
VIDIATION				along x,y,z axes for 6 cycles
MTBF	according to MIL-HDBK-217F	GB	+25°C	100 x 10 ³ hours
		, u.b.	+70°C	17 x 10 ³ hours

Derating Graph



RAC04-GB Series

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

OAFETV			
SAFETY	and cei	кпеюаі	IUNS

Certificate Type (Safety)	Report / File Number	Standard
nformation Technology Equipment, General Requirements for Safety		UL60950-1, 2nd Edition, 2014
	E196683-A4	CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014
Audio/video, information and communication technology equipment. Safety requirements		UL62368-1, 2nd Edition
		CAN/CSA C22.2 No 62368-1-14
nformation Technology Equipment, General Requirements for Safety	SA1703184S 001	EN60950-1: 2006 + A2, 2013
nformation Technology Equipment, General Requirements for Safety (CB)	0/11/001040 001	IEC60950-1, 2nd Edition: 2005 + AM2, 2013
Audio/video, information and communication technology equipment. Safety requirements	4787985921-	EN62368-1: 2014
Audio/video, information and communication technology equipment. Safety requirements (CE	20171025	IEC62368-1, 2nd Edition: 2014
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V	CA 1700104L 00001	EN61558-1: 2005 + A1, 2009
Safety of power transformers, power supplies, reactors and similar products for supply voltages up to 1100 V Part 2: Particular requirements	- SA 1709184L 02001	EN61558-2-16: 2009 + A1, 2013
EAC	RU-AT.03.67361	TP TC 004/020, 2011
RoHS 2+		RoHS 2011/65/EU + AM2015/863
RoHS 2+ EMC Compliance	Condition	Standard / Criterion
	Condition EA1703184E 01001	
EMC Compliance Information technology equipment - Radio disturbance		Standard / Criterion
EMC Compliance Information technology equipment - Radio disturbance characteristics - Limits and methods of measurement ⁽⁹⁾ Limitations on the amount of electromagnetic intererence allowed from digital and	EA1703184E 01001	Standard / Criterion EN55032: 2015, Class E
EMC Compliance Information technology equipment - Radio disturbance characteristics - Limits and methods of measurement ⁽⁹⁾ Limitations on the amount of electromagnetic intererence allowed from digital and electronic devices	EA1703184E 01001 EA1703184F 01001 Air ±8kV	Standard / Criterion EN55032: 2015, Class E 47 CFR FCC Part 15 Subpart B: 2016
EMC Compliance Information technology equipment - Radio disturbance characteristics - Limits and methods of measurement ⁽⁹⁾ Limitations on the amount of electromagnetic intererence allowed from digital and electronic devices ESD Electrostatic discharge immunity test	EA1703184E 01001 EA1703184F 01001 Air ±8kV Contact ±4kV	Standard / Criterion EN55032: 2015, Class E 47 CFR FCC Part 15 Subpart B: 2016 EN61000-4-2: 2009, Criteria A
EMC Compliance Information technology equipment - Radio disturbance characteristics - Limits and methods of measurement ⁽⁹⁾ Limitations on the amount of electromagnetic intererence allowed from digital and electronic devices ESD Electrostatic discharge immunity test Radiated, radio-frequency, electromagnetic field immunity test	EA1703184E 01001 EA1703184F 01001 Air ±8kV Contact ±4kV 3V/m	Standard / Criterion EN55032: 2015, Class E 47 CFR FCC Part 15 Subpart B: 2016 EN61000-4-2: 2009, Criteria A EN61000-4-3: 2006 + A2, 2010, Criteria A
EMC Compliance Information technology equipment - Radio disturbance characteristics - Limits and methods of measurement ⁽⁹⁾ Limitations on the amount of electromagnetic intererence allowed from digital and electronic devices ESD Electrostatic discharge immunity test Radiated, radio-frequency, electromagnetic field immunity test Fast Transient and Burst Immunity	EA1703184E 01001 EA1703184F 01001 Air ±8kV Contact ±4kV 3V/m AC Port ±1kV	Standard / Criterion EN55032: 2015, Class E 47 CFR FCC Part 15 Subpart B: 2016 EN61000-4-2: 2009, Criteria A EN61000-4-3: 2006 + A2, 2010, Criteria A EN61000-4-4: 2012, Criteria A
EMC Compliance Information technology equipment - Radio disturbance characteristics - Limits and methods of measurement ⁽⁹⁾ Limitations on the amount of electromagnetic intererence allowed from digital and electronic devices ESD Electrostatic discharge immunity test Radiated, radio-frequency, electromagnetic field immunity test Fast Transient and Burst Immunity Surge Immunity	EA1703184E 01001 EA1703184F 01001 Air ±8kV Contact ±4kV 3V/m AC Port ±1kV AC Port ±1kV	Standard / Criterion EN55032: 2015, Class E 47 CFR FCC Part 15 Subpart B: 2016 EN61000-4-2: 2009, Criteria A EN61000-4-3: 2006 + A2, 2010, Criteria A EN61000-4-3: 2016, Criteria A EN61000-4-5: 2014, Criteria E EN61000-4-6: 2014, Criteria A
EMC Compliance Information technology equipment - Radio disturbance characteristics - Limits and methods of measurement ⁽⁹⁾ Limitations on the amount of electromagnetic intererence allowed from digital and electronic devices ESD Electrostatic discharge immunity test Radiated, radio-frequency, electromagnetic field immunity test Fast Transient and Burst Immunity Surge Immunity	EA1703184E 01001 EA1703184F 01001 Air ±8kV Contact ±4kV 3V/m AC Port ±1kV AC Port L-N ±1kV AC Power Port 3V	Standard / Criterion EN55032: 2015, Class E 47 CFR FCC Part 15 Subpart B: 2016 EN61000-4-2: 2009, Criteria A EN61000-4-3: 2006 + A2, 2010, Criteria A EN61000-4-4: 2012, Criteria A EN61000-4-5: 2014, Criteria E


Note9: If output is connected to GND, please contact RECOM tech support for advice

DIMENSION AND PHYSICAL CHARACTERISTICS				
Parameter	Туре	Value		
Material	case PCB	black plastic, (UL94V-0) FR4, (UL94V-0)		
Dimension (LxWxH)		37.0 x 24.0 x 15.0mm		
Weight		20g typ.		

RAC04-GB

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Series



PACKAGING INFORMATION				
Parameter	Туре	Value		
Packaging Dimension (LxWxH)	tube	505.0 x 39.7 x 23.2mm		
Packaging Quantity		20pcs		
Storage Temperature Range		-40°C to +100°C		
Storage Humidity	non-condensing	5% -95% RH max.		

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.