Piezo Siren

1. Scope

This specification is applied to Piezo Siren (Self-Drive Type) The product described below is used as a buzzer in various alarm systems


2. Basic Condition

- 2.1 Rated Voltage:12VDC
- 2.2 Operating Voltage:8~16VDC
- 2.3 Operating Temperature Range:-20 ºC~+70 ºC
- 2.4 Storage Temperature Range:-30°C~+80 °C


3. Electrical Characteristics

- 3.1 Sound Press Level:Level: \geq 100dB at 100cm / 12VDC
- 3.2 Consumption Current: ≦250mA at 12VDC
- 3.3 Resonate Frequency:4400Hz±500Hz
- 3.4 Tone Nature: Siren Sound
- 3.5 Material:ABS

4. Measuring Method



5. Sound Press Level & Consumption Current Curve





onents

Distrelec Schweiz AG, Grabenstrasse 6, 8606 Nänikon, Switzerland, T+41 44 944 99 11, info@distrelec.com, distrelec.com

TEST REPORT

#	dB	mA	Hz
1	108	124	4578
2	108	134	4598
3	107	131	4603
4	108	124	4590
5	108	126	4530

Remark:

(1)Sound Press Level : \geq 100dB at 100cm / 12VDC (2)Consumption Current : \leq 250mA at 12VDC

(3)Resonate Frequency : 4400Hz±500

6. Environment Test Method

NO.	ITEM	TEST CONDITION AND REQUIREMENT	
1	High Temperature Test (Storage)	After being placed in a chamber with 80±2°C for 96 hours and then being placed in normal condition for 2 hours. Allowable variation of SPL after test: ±10dB.	
2	Low Temperature Test (Storage)	After being Placed in a chamber with -30±2°C for 96 hours and then being placed in normal condition for 2 hours. Allowable variation of SPL after test: ±10dB.	
3	Humidity Test	After being Placed in a chamber with 90-95% R.H. at $40\pm2^{\circ}$ C for 96 hours and then being placed in normal condition for 2 hours. Allowable variation of SPL after test: \pm 10dB.	
4	Temperature Cycle Test	The part shall be subjected to 5 cycles. One cycle shall be consist of: +80°C +25°C -30°C	
5	Drop Test	Drop on a hard wood board of 4cm thick, any directions ,6 times, at the height of 100cm. Allowable variation of SPL after test: ± 10 dB.	
6	Vibration Test	After being applied vibration of amplitude of 1.5mm with 10 to 55 Hz band of vibration frequency to each of 3 perpendicular directions for 2 hours. Allowable variation of SPL after test: ±10dB.	
7	Solder ability Test	Lead terminals are immersed in rosin for 5 seconds and then immersed in solder bath of +300±5°C for 3±1 seconds.90% min. lead terminals shall be wet with solder (Except the edge of terminals).	
8	Terminal / Wire Strength Pulling Test	The force of 9.8N(1.0kg) is applied to each terminal in axial direction for 10 seconds. No visible damage and cutting off.	


7. Reliability Test

Continuous life test:

250 Hours continuous operating at +70 °C with maximum rated voltage applied . Intermittent life test:

Aduty cycle of 1 minute on, 5 minutes off, a minimum of 10000 times at temperature +25 °C±2

8. Dimensions



Tolerance ±0.5mm