Features

- Low Cost 230VAC LED Power Supply
- 0-10V dimmable

LED Driver

Description

for installation inside furniture.

- Active Power Factor Correction >0.9
 Designed to drive 15W 46W 000 LEF
- Designed to drive 15W-46W COB LEDs
 Terminal Block Input/Output with Cable Clamps

Fully Protected (OLP, SCP, OCP, OTP)

Suitable for Class I and Class II Luminaires

RECOM AC/DC Converter

RCOB-A

Dimmable Active PFC Single Output

Selection Guide Part Input Output Output Efficiency Max. Rated Number Voltage Range Voltage Range Current typ. Power (VDC) (VAC) (mA) (%) (W) RCOB-350A 198-264 6-44 0-350 80 15 RCOB-700A 198-264 6-44 0-700 84 31 RC0B-1050A 198-264 6-44 0-1050 83 46

These ErP-compliant COB LED drivers are available with three preset output currents: 350mA, 700mA

and 1050mA. They are designed to drive COB (Chip On Board) high power LEDs with a forward voltage between 6V and 44VDC from a 230VAC supply (198-264VAC). They operate with efficiencies of up to

84%, feature active PFC and are fully protected against short circuit, output overvoltage, open-circuit and over-temperature conditions. The output current is dimmable over a 0%-100% range with a 0-10V external control voltage. The LED drivers are suitable for both independent and built-in installations and

All LED Drivers may not be used without a load. They must be switched on the primary side only. Noncompliance may damage the LED or reduce its lifetime.


Specifications (measured at TA= 25°C, nominal input voltage, rated load)


BASIC CHARACTERISTICS				
Parameter	Condition	Min.	Тур.	Max.
Input Voltage Range		198VAC	230VAC	264VAC
Output Voltage Range	full load	6VDC		44VDC
absoulute max. Output Voltage	full load			58VDC
Inrush Current	at 230VAC		5.5A / 10µs	
Start-up Time	at 230VAC		≤0.5 Second	
Input Frequency		47Hz	50Hz	63Hz
Efficiency			see S	election Guide
Output Current Accuracy	low line to high line, full load		±6%	
Power Factor	full load, 230VAC		0.9	



EN-61347-1 Compliant EN-61347-2-13 Compliant EN-55015 Compliant EN-61547 Compliant EN-61000-3-2 Compliant EN-61000-3-3 Compliant

Derating Graph





Efficiency


Refer to Applications Notes

RECOM AC/DC Converter

RCOB-A Series

Specifications (measured at TA= 25°C, nominal input voltage, rated load)





PROTECTION

FNULCTION		
Parameter	Condition	Value
Short Circuit Protection (SCP)	230VAC / 50Hz	constant current limit at Inominal and recovers after fault condition is removed
Over Load Protection (OLP)	230VAC / 50Hz	power limiting, if forward voltage of LED's is higher than 44VDC
Output Over Voltage Protection (OVP)	230VAC / 50Hz	58V max.
Output Over Current Protection (OCP)	230VAC / 50Hz	constant current source
Over Temperature Protection (OTP)		automatic recovery after cool down
Isolation Voltage		3kVAC / 1 minute
Surge Capacity	L-N	2kV
	L,N-FG	4kV

Maximum loading of automatic circuit breakers*

* @ 115VAC, 10hm, 90° phase angle and max. load

Power	Circuit Breaker Circuit Breaker Current		t		
TOWCI	Тур	10A	16A	20A	25A
\geq 7W	С	101	128	171	228
≥15W	С	47	68	84	105
≥ 25W	С	32	48	57	72
≥ 35W	С	22	35	39	55
\geq 45W	С	16	28	31	43

* @ 230VAC, 10hm, 90° phase angle and max. load

Power	Circuit Breaker	Circuit Breaker Current			
TOWCI	Тур	10A	16A	20A	25A
> 714/	В	61	100	121	150
≥7W	С	121	164	221	291
> 1EW	В	35	57	69	85
≥ 15W	С	57	87	109	134
	В	24	38	46	58
≥ 25W	С	38	62	74	92
	В	18	30	35	43
≥ 35W	С	29	46	55	69
	В	17	28	33	41
≥ 45W	С	24	39	47	57

* @ 277VAC, 10hm, 90° phase angle and max. load

Power	Circuit Breaker	Circuit Breaker Current			
10000	Тур	10A	16A	20A	25A
> 7W	В	61	100	121	150
≥ / ₩	С	121	164	221	291
> 1EW	В	35	57	69	85
≥15W	С	57	87	109	134
	В	24	38	46	58
≥ 25W	С	38	62	74	92
	В	18	30	35	43
≥ 35W	С	29	46	55	69
	В	17	28	33	41
≥ 45W	С	24	39	47	57

RECOM AC/DC Converter

RCOB-A Series

Specifications (measured at TA= 25°C, nominal input voltage, rated load)

ENVIRONMENTAL

EINVINUMIVIENTAL		
Parameter	Condition	Value
Operating Temperature Range max. Case Temperature Range	All Types RCOB-350A RCOB-700A RCOB-1050A	-20°C to +50°C, Ambient 80°C max., Ambient 85°C max., Ambient 90°C max., Ambient
Storage Temperature Range		-30° to +80°C, Ambient
Storage Humidity		30% - 95% RH
Operating Humidity	RCOB-1050A RCOB-350 and RCOB-700A	45% to 85% RH 5% to 85% RH, non condensing
MTBF	at Tc= 70°C; lout: 350mA at Tc= 70°C; lout: 700mA, 1050mA	45 x 10 ³ hours 50 x 10 ³ hours


SAFETY AND CERTIFICATIONS		
Certificate Type		Standard
CE General Safety	compliant	EN-61347-1
CE Safety of AC supplied Control Gear for LED Modules	compliant	EN-61347-2-13
RoHS	compliant	RoHS 6/6
Certificate Type (Environmental)		Standard / Criterion
Electric Lighting, EMC Immunity	compliant	EN-61547
Electric Lighting, EMC Emissions	compliant	EN55015, Class B
Limits for Harmonic Emissions EMC Compatability: Flicker and Voltage Variations	compliant	EN-61000-3-2 EN-61000-3-3
IP Rating		IP20


Parameter	Туре	Value
Case Material		integrated cable clamps, Plastic
Dimensions (LxWxH)	RCOB-350A; RCOB-700A RCOB-1050A	106 x 67 x 22mm 121.7 x 78 x 22mm
Weight	RCOB-350A; RCOB-700A RCOB-1050A	130g 180g
Packaging Dimension (LxWxH)	Cardboard Box	12.5 x 8.2 x 3.8mm
Packaging Quantity		10pcs



Specifications (measured at TA= 25°C, nominal input voltage, rated load)


Mechanical Dimensions





Series

RCOB-A








Specifications (measured at TA= 25°C, nominal input voltage, rated load)





The product information and specifications are subject to change without prior notice. RECOM products are not authorized for use in safety-critical applications (such as life support) without RECOM's explicit written consent. A safety-critical application is defined as an application where a failure of a RECOM product may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The buyer shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.