Features

Unregulated

Converters

- Low cost 1W converter
- Industry standard pinout
- SIP4 package
- 1kVDC isolation
- Efficiency up to 79%
- Wide operating temperature range -40°C to +85°C
- UL60950-1, CAN/CSA C22.2 No. 60950-1 certified

RECO DC/DC Converter

RFM

1 Watt SIP4 Single Output









UL60950-1 certified CAN/CSA-C22.2 No 60950-1 certified EN55032 compliant

Description

The RFM DC/DC converter is typically used in cost sensitive general purpose power isolation and voltage matching applications. Despite its low cost, it is a fully specified converter with 1kVDC isolation, industrial operating temperature range of -40°C to +85°C without derating and UL/ EN certifications.

Selection Gui	ide				
Part Number	Input Voltage [VDC]	Output Voltage [VDC]	Output Current [mA]	Efficiency ⁽¹⁾ typ. [%]	Max. Capacitive Load ⁽²⁾ [μF]
RFM-0505S	5	5	200	79	470

Notes:

Note1: Efficiency is tested at nominal input and full load at +25°C ambient Note2: Max. Cap Load is tested at nominal input and full resistive load

Model Numbering



Specifications (measured @ Ta= 25°C, nominal input voltage, full load and after warm-up)

BASIC CHARACTERISTICS					
Parameter	Condition	Min.	Тур.	Max.	
Internal Input Filter				capacitor	
Input Voltage Range			±10%		
Input Current	max. load		250mA		
Quiescient Current	nom. Vin = 5VDC		25mA	30mA	
Minimum Load (3)		0%			
Internal Operating Frequency		50kHz	80kHz	100kHz	
Output Ripple and Noise (4)	20MHz BW		50mVp-p	100mVp-p	
Reflected Back Ripple Current	20MHz BW, no external choke		20mAp-p		

Notes:

Note3: Operation below 10% load won't harm the converter, but specifications may not be met

Note4: Measurements are made with a 100nF MLCC across output (low ESR)


continued on next page



RFM

Series

Specifications (measured @ Ta= 25°C, nominal input voltage, full load and after warm-up)



REGULATIONS		
Parameter	Condition	Values
Output Accuracy		±5.0% max.
Line Regulation	low line to high line, full load	±1.2% typ. / ±1% max.
Load Regulation	10% to 100%	±10% typ. / ±15% max.
Tolerance Envelope	+15% +5% Vnom Vnom Vnom Vnom Vnom Vnom Vnom Vnom	+5% -1% -5%
	10 50	100
	Output Load [%]	

PROTECTIONS			
Parameter		Condition	Value
Isolation Voltage (5)	I/P to O/P	tested for 1 second	1kVDC
Isolation Resistance			1G Ω min.
Isolation Capacitance			75pF max.
Leakage Current	50	00VAC, 50Hz	1μA max.
Insulation Grade			Functional
	Notes:		

Note5: For repeat Hi-Pot testing, reduce the time and/or the test voltage



RFM


Series

Specifications (measured @ Ta= 25°C, nominal input voltage, full load and after warm-up)

ENVIRONMENTAL				
Parameter	Condition		Value	
Operating Temperature Range	(@ natural convection 0.1m/s) (see graph)	without derating	-40°C to +85°C	
Maximum Case Temperature			+105°C	
Temperature Coefficient			±0.05%/°C	
Thermal Impedance	0.1m/s, horizontal directi	0.1m/s, horizontal direction		
Operating Altitude			2000m	
Operating Humidity	non-condensing		95% RH max.	
Pollution Degree			PD2	
Vibration			MIL-STD-202G	
MTBF	according to MIL-HDBK-217F, G.B.	+25°C	20100 x 10 ³ hours	
INITOI	according to MIL-HDBK-217F, G.B.	+85°C	8700 x 10 ³ hours	


Derating Graph

(@ Chamber and natural convection 0.1 m/s)



SAFETY AND CERTIFICATIONS Certificate Type (Safety) Report/File Number Standard UL60950-1, 2nd Edition, 2007 Information Technology Equipment, General Requirements for Safety E358085-A4 CSA C22.2 No. 60950-1-07, 2nd Edition, 2007 RoHS 10/10, 2015 RoHs 2+ **EMC Compliance** Condition Standard / Criterion Information technology equipment - Radio disturbance with external filter EN55032, Class A, B characteristics - Limits and methods of measurement (see below filter suggestion)

EMC Filtering - Suggestions for Class A and B



Component List Class A			
C1	L1	C2	C3
6.8µF	-	-	-

Component List Class B			
C1	L1	C2 and C3	
10μF	22µH	330pF/1kV	




RFM

Series

Specifications (measured @ Ta= 25°C, nominal input voltage, full load and after warm-up)

DIMENSION AND PHYSICAL CHARACTERISTICS				
Parameter	Туре	Value		
Material	case	non-conductive black plastic (UL94 V-0)		
Waterial	potting	epoxy (UL94 V-2)		
Package Dimension (LxWxH)		11.5 x 6.0 x 10.0mm		
Package Weight		1.4g		



Pin #	Function	
1	-Vin	
2	+Vin	
3	-Vout	
4	+Vout	

Pin Connections

Tolerance: $xx.x = \pm 0.5$ mm $xx.xx = \pm 0.25$ mm

Pin tolerance:
Thickness: ±0.05mm
Lenght: +0.25/-0.50mm

PACKAGING INFORMATION			
Parameter	Туре	Value	
Packaging Dimension (LxWxH)	tube	520.0 x 16.0 x 9.0mm	
Packaging Quantity		42pcs	
Storage Temperature Range		-55°C to +125°C	
Storage Humidity		5% - 95%, RH	

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.