



Product: RKCCS 5L ☑


M12 Power Field Attachable Connector: Female, straight, 5-pin(4+FE), L-coded, shielded, silver housing, crimp type, 50 V AC/60 V DC

# **Product Description**

M12 Power Field Attachable Connector: Female, straight, 5-pin(4+FE), L-coded, shielded, silver housing, crimp type, 50 V AC/60 V DC

### **Technical Drawing**





### **Technical Specifications**

### **Technical Data**

Product Sub Family: M12	wer Connector 2 Power
·	2 Power
Brand: Lumb	mberg Automation
Connector Type: Field	ld attachable
Type of Contact / Gender: fema	nale
Connector Design: straig	aight
Number of Pins: 5(4+f	+FE)
Coding:	
Shielding: Shiel	ielded
Attachment Type: Coup	upling Nut
Rated Voltage: 63 V	V
Rated Impulse Voltage: 1.5 k	kV
Operating Voltage: 50 V	V AC / 60 V DC
Contact Resistance: ≤ 10	0 mOhm
Insulation Resistance: > 10'	0^9 Ohm
Mating Cycles: ≤ 100	00
Type of Connection: crimp	np
Cable Gland: PG 1	11
Maximum Wire Isolation Diameter: max.	x. Ø2,9 mm

Strain-Relief:	clamping cage	
Suitable Cables:	3 gaskets enclosed (Ø3 - Ø6 mm, Ø5 - Ø9 mm, Ø8 - Ø11 mm)	
Ambient Temperature (Operation)*:	-40 °C to +125 °C, notice derating	
Protection Degree / IP Rating**:	IP65, IP67	
Design Standard:	IEC 61076-2-111	
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)	
Clearance / Creepage Distance:	e: DIN EN 60664-1 (2008/01); VDE 0110-1	
Overvoltage Category:	III acc. to DIN EN 60664-1 (VDE 0110-1)	

#### **Materials**

Contact Base Material:	CuNi
Contact Plating:	Cu/Au
Contact Bearer Material:	PBT GF
Contact Bearer Color:	grey
Flammability Class (Contact Bearer):	UL 94 V-2
Housing Material:	CuZn
Housing Plating:	Ni
Housing Color:	silver
Cable Gland Material:	CuZn
Cable Gland Plating:	Ni
Cable Gland Gasket:	NBR
Strain-Relief Material:	PBT GF
Flammability Class (Strain Relief):	UL 94 V-2
Attachment Material:	CuZn
Attachment Plating:	Cu/Ni
Shielding Material:	CuZn, plating: Ni
O-Ring Material:	FKM

#### **Additional Technical Data**

Fastening Torque (Contact Screw): M 12x1: (50-60) Ncm, hand-tight

### Safety & Environmental Compliance

RoHS Compliant: yes

#### **Notes**

Note Derating:	* Notice derating	
Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.	
Product Characteristics:	To ensure ingress protection, please check the O-ring's position before connecting. Improperly positioned O-ring leads to ingress protection potential failure.	

#### Variants

	Item #	Item Description	<b>Conductor Cross Section</b>	Rated Current
	934935005	RKCCS 5L/11 1,5	1.5 mm <sup>2</sup>	16 A
	934935006	RKCCS 5L/11 2,5	2.5 mm <sup>2</sup>	16 A

## © 2021 Belden, Inc

#### All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.