

## SPECIFICATIONS:

ELECTRICAL LIFE: 30,000 make-and-break cycles at full load.  
 CONTACT RESISTANCE: 20mΩ max. initial @ 2-4VDC.  
 INSULATION RESISTANCE: 1000MΩ min.  
 DIELECTRIC STRENGTHS: 1,500VRMS @ sea level.  
 OPERATING TEMPERATURE:-30°C to +85°C.

## MATERIALS:

CASE: Diallyl phthalate(DAP)(UL 94V-0).  
 ROCKER: Nylon 6/6 (UL 94V-0).  
 BUSHING: Zinc, nickel plated.  
 HOUSING: Stainless Steel.  
 SWITCH SUPPORT: Brass, tin plated.  
 TERMINAL SEAL: Epoxy.

Art. Nr.  
**RND 210-00512**

