# **PCB Tact Switch**

## PCB 12 VDC 50 mA Through Hole THT



#### **FEATURES:**

Contact Resistance:100m-ohms max. @ 1A 2 - 4 VDC
Insulation Resistance:100M-ohms max. @ 500VDC
Withstand Voltage: 100VAC RMS for 1 min
Endurance: 10.000 cycles @ 10 cpm


Total Travel: 0.25 mm


#### SPECIFICATION:


Switching type	Momentary function
Switching type, ()momentary	(on)-off
Rated current	50 mA
Rated voltage	12 VDC
Actuation force	1.57 N
Poles	1
Mounting	Through Hole THT
Termination type	PCB
Colour	black/grey
Temperature range	-20+70 °C
Construction form	Tact switch
Height	4.3 mm
Length	12 mm
Width	12 mm




#### **DRAWING**









### Art Nr:

RND 210-00197