

# Resistance Thermometer with DIN B Head



## Features

- This thermometer utilizes a Pt100 sensor, which is known for its high accuracy and stability in temperature measurement
- It is suitable for applications where precise temperature control and measurement are crucial
- This design ensures durability and allows for easy installation in various industrial environments



## Specification

Sensor Type	Pt100 (100 Ohms @ 0°C) to IEC 751, Class B, 4 Wire
Probe Material	316SS
Cable Termination	DIN B Termination
Process Connection Cable	Stainless Steel Plug
Entry	PG16
Probe Temperature Range	-50 °C to 450 °C (Connection Head @ 170 °C)

## Order Codes

Probe DiaØ	Probe Length	Order code
6.0 mm	300 mm	RND 410-00330