

PCB Tact Switch

PCB 12 VDC 50 mA Through Hole THT



FEATURES:


Contact Resistance: 100m-ohms max. @ 1A 2 - 4 VDC
 Insulation Resistance: 100M-ohms max. @ 500VDC
 Withstand Voltage: 100VAC RMS for 1 min
 Endurance: 10.000 cycles @ 10 cpm
 Total Travel: 0.25 mm

SPECIFICATION:

Switching type	Momentary function
Switching type, () momentary	(on)-off
Rated current	50 mA
Rated voltage	12 VDC
Actuation force	2.45 N
Poles	1
Mounting	Through Hole THT
Termination type	PCB
Colour	black/grey
Temperature range	-20...+70 °C
Construction form	Tact switch
Height	8.5 mm
Length	12 mm
Width	12 mm



DRAWING



Art Nr:

RND 210-00202