

PCB Tact Switch

PCB 12 VDC 50 mA SMT



FEATURES:


- Contact Resistance: 100m-ohms max. @ 1A 2 - 4 VDC
- Insulation Resistance: 100M-ohms max. @ 500VDC
- Withstand Voltage: 100VAC RMS for 1 min
- Endurance: 10.000 cycles @ 10 cpm
- Total Travel: 0.25 mm

SPECIFICATION:

Switching type	Momentary function
Switching type, () momentary	(on)-off
Rated current	50 mA
Rated voltage	12 VDC
Actuation force	1.57 N
Poles	1
Mounting	SMT
Termination type	PCB
Colour	black/grey
Temperature range	-20...+70 °C
Construction form	Tact switch
Height	7 mm
Length	6 mm
Width	6 mm



DRAWING



DIM. "A" = 7 mm

Type	DIM. "A"
RND 210-00203	.169 [4.30]
RND 210-00204	.197 [5.00]
RND 210-00205	.276 [7.00]
RND 210-00207	.374 [9.50]