

Features

- Wheels
- Extendable handle
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Polyamide pins, corrosion free
- Convoluted foam in the lid and cubed foam in the bottom to protect your objects



Specification

IP67 RATING **ATA 300** **MIL SPECS** DEF STAN 81-41
STANAG 4280

External Dimensions	574 x 361 x 225mm
Internal Dimensions	520 x 290 x 200 mm
Cover Depth - Bottom	155 + 45 mm
Weight	5.06 kg
Temperature Range	-30 ... 90 °C
Capacity	30.16l
Protection Rating	IP67

Material Specification

Base	Polypropylene Copolymer
Latches	Polyamide
O-Ring	Polymer
Moulding	Injection Moulded

Art. Nr.
RND 550-00513

