

## SPECIFICATIONS:

- BUSHING:  $\varnothing 19\text{mm}$ .
- CONTACT RATING: 5A @ 250VAC.
- ELECTRICAL LIFE: 50,000 cycles at full load.
- CONTACT RESISTANCE: 50m-ohms max. initial @2-4VDC.
- INSULATION RESISTANCE: 1,000M-ohms min. @500VDC.
- DIELECTRIC STRENGTH: 2,000V RMS 50~60Hz.
- IP CLASS: IP40 & IK02 protection.
- TORQUE: 0.6Nm max. applied to nut.
- CONSTRUCTION FORM: DPDT.
- SWITCHING CIRCUIT: 45° 3 positions ON-ON (maintained).
- OPERATING TEMPERATURE:  $-20^{\circ}\text{C} \sim +55^{\circ}\text{C}$ .



## MATERIALS:

- CONTACT: Silver alloy.
- BUSHING: Stainless steel.
- BASE: PBT.
- NUT: Nickel plated brass.

**Art. Nr.**  
**RND 210-00421**

Specifications and Dimensions subject to change

