

PCB Relay, 12VDC, 270 Ohm



Features

- Creepage distance:8.0mm Min
- Au-clad contact available
- Transparent sealed available
- Class B/F available

Specification

Nominal Voltage (VDC)	12
Coil Resistance (Ω)	270
Rated Current (mA)	45
Max Operate Voltage (VDC)	9.6
Min Release Voltage (VDC)	0.6
Coil Power (W)	0.54

Art. Nr.
RND 200-00046

PCB Relay, 12VDC, 270 Ohm



Contact Data





Contact Material	Silver Alloy
Load	Resistive load(COS Φ =1)
Contact Ratings	5A 240VAC 5A 30VDC
Minimum load	100mA 5VDC
Max Switching Voltage	250VAC/30VDC
Max Switching Current	8A
Max Switching Power	1250VA/240W
Contact Resistance	100m Ω Max at 6VDC 1A
Life Expectancy	Electrical: 100,000 Operations(at30Operations/minute)
	Mechanical: 10,000,000 Operations(at300Operations/minute)

Characteristics Data

Insulation Resistance	100M Ω Min at 500VDC
Dielectric Strength Between Open Contacts	1000VAC(for one minute)
Between Contacts and coil	5000VAC(for one minute)
Operate Time	20ms
Release Time	10ms
Temperature Range	-40 $^{\circ}$ Cto+70 $^{\circ}$ C
Shock Resistance	Operating Extremes: 10G
	Damage Limits: 100G
Vibration Resistance	10-55Hz, 1.5mm
Max. switching frequency	Mechanical: 18,000 operations/hr Electrical: 1,800 operations/hr
Humidity	40-85%
Weight	Approx 14g
Safety Standard	UL cUL TÜV CQC

PCB Relay, 12VDC, 270 Ohm

Engineering Data



Overall and Mounting Dimensions

