Lithium Battery 1/2 AA



Features

- High and stable operating voltage
- \bullet Low self discharge rate(less than 1% after 1 year of storage at 25 $^{\circ}\text{C}$)
- Long storage life
- Stainless steel container(with low magnet)
- Widely operating temperature range
- Hermetic glass-to-metal sealing
- Non-flammable electrolyte
- CE,UL,SGS recognized, ISO9001 approved


Applications

- Utility metering
- Memory back-up
- Alarms and security devices
- Tollgate systems
- Military electronics
- Automotive electronics
- Professional electronics
- GPS tracking
- Real time clock

Specification

| Nominal Capacity | 1.2 Ah |
|-----------------------------|--------------|
| Nominal Voltage | 3.6 V |
| Max. Continuous Current | 25 mA |
| Max. Pulse Capability | 50 mA |
| Storage (Recommended) | 30 °C max. |
| Operating Temperature Range | -60 85 °C |
| Weight | Approx. 11 g |

Drawing







Lithium Battery 1/2AA




Discharge Characteristics (25 °C)



Voltage Versus Temperature



Capacity Versus Current



Art. Nr. RND 305-00029

Warning

- •It is strictly forbidden to have the battery positive and negative short circuit, charging, discharging, heating over 100 °C remove, anatomy, or may cause explosion, combustion, internal acid leakage
- Do not solder directly on the battery, should use wire or nickel sheet by pre spot welded
- Can not mixed use with old and new battery or mixed use different kinds battery
- Don't assemble the batteries from different manufacturers
- Do not use the battery over the temperature range
- Discharged battery should be buried deeply in the ground