D-Sub to IDC Connector



Features

- Contact casing in tin-plated steel
- With low depth from flange
- For simpler applications with fewer mating cycles




Specification

Number of Poles	15	
Gender of Contacts	Female	
Connection A	D-SUB 15-Pin	
Connection B	IDC	
Operating Temperature Range	-45 85 °C	
Rated Current	3 A	
Dielectric Withstand Voltage	AC 1000 V RMS	
Insulation Resistance	500 M Ω min. at DC 500 V	
Contact Resistance	$25\ m\Omega$ max.	
Cable Cross Section	28 26 AWG	

Material Specification

Housing Material	Steel, Tin-Plated
Contact Material	Brass, Gold-Flashed
Insulator	PBT, UL 94 V-0

Drawing



A	39.1 mm
В	33.3 mm
С	24.6 mm
D	26.9 mm