# TNC PLUG FOR RG58 CABLE



#### **Features**

- TNC (Threaded Neill-Concelman) connectors are designed for RF (Radio Frequency) applications and are commonly used with coaxial cables like RG58.
- TNC connectors are suitable for a wide frequency range for various RF applications such as telecommunications, wireless networks, and RF testing
- TNC connectors offer a good compromise between ease of use, robustness, and frequency performance for RG58 cables




### **Specification**

Impedance	50 Ohm	
Frequency Range	0 3 GHz	
VSVR	1.5 max	
Working Voltage	500 V RMS @ Sea Level	
Insulation Resistance	5 GOhm min.	
Temperature Range	-55 155 ℃	

# **Material Specification**

Body	Brass, Nickel
Insulator	PTFE
Center Pin	Brass, Gold

# **Drawing**



Art. Nr. RND 205-01505