


# Rotary DIP Switch

HEX 4+1



| Position | Common C contacted ● |   |   |   |   |
|----------|----------------------|---|---|---|---|
|          | 1                    | 2 | 4 | 8 | C |
| 0        |                      |   |   |   | ● |
| 1        | ●                    |   |   |   | ● |
| 2        |                      | ● |   |   | ● |
| 3        | ●                    | ● |   |   | ● |
| 4        |                      |   | ● |   | ● |
| 5        | ●                    |   | ● |   | ● |
| 6        |                      | ● | ● |   | ● |
| 7        | ●                    | ● | ● |   | ● |
| 8        |                      |   |   | ● | ● |
| 9        | ●                    |   |   | ● | ● |
| A        |                      | ● |   |   | ● |
| B        | ●                    | ● |   | ● | ● |
| C        |                      |   | ● |   | ● |
| D        | ●                    |   | ● |   | ● |
| E        |                      | ● | ● |   | ● |
| F        | ●                    | ● | ● | ● | ● |

## SPECIFICATION:

|                    |               |
|--------------------|---------------|
| Switching type     | HEX           |
| Row spacing        | 5.08 mm       |
| Pins               | 4+1           |
| Pitch              | 2.54 mm       |
| Actuation          | side          |
| Switching capacity | 0.5 A@ 24 VDC |
| Contact resistance | <100 mΩ       |
| Contact material   | Gold-plated   |
| Test voltage       | 300 VAC       |
| Temperature range  | -10...+70 °C  |

Art. Nr.

RND 210-00126