

Features


- Brass fittings are known for their excellent corrosion resistance, making them suitable for various applications, especially in environments where exposure to moisture or harsh substances is common
- The material's strength and ability to withstand pressure, temperature variations, and mechanical stress
- Brass fittings are highly versatile and find applications in a wide range of industries



Specification

Material	Brass
Medium	Air, Water
Temperature	- 20 ° C ~ 80 ° C
Thread	BSPT
Tolerance	Up to 10 mm and ± 0.1 mm from 12 ~ 14 mm
Burst Pressure	Must not exceed 30 bar

Product Range & Drawing



Part Number	$\phi D1$ (mm)	$\phi D2$ (mm)	L1 (mm)	L2 (mm)	H (mm)	T	S (mm)
RND 425-00194	11.6	6	22.5	22.5	7.5	R 1/8	10
RND 425-00195	11.6	6	22.5	24.5	9.5	R 1/4	14
RND 425-00196	13.5	8	25	23	7.5	R 1/8	12
RND 425-00197	13.5	8	25	25	9.5	R 1/4	14
RND 425-00198	13.5	8	25	26	10.5	R 3/8	17
RND 425-00199	15.5	10	27.5	27.5	9.5	R 1/4	14
RND 425-00200	15.5	10	27.5	28.5	10.5	R 3/8	17
RND 425-00201	15.5	10	27.5	31.5	13.5	R 1/2	21
RND 425-00202	17.8	12	29.5	29	9.5	R 1/4	17
RND 425-00203	17.8	12	29.5	30	10.5	R 3/8	17
RND 425-00204	17.8	12	29.5	33	13.5	R 1/2	21