

P40 A JUNIOR Piezoelectric Sounder



RND 430-00113 (12/24V) AC/DC



RND 430-00114 (90/240V) AC

Buzzer piezoelettrico multifunzione.

Multi-function piezoelectric sounder.

Buzzer piézoélectrique multifonctionne.

Multifunktionaler piezoelektrischer Schallgeber.

Sirena piezoeléctrica multifunción

CUPOLA DOME DOME HAUBE CÚPULA	PC														
CORPO BODY CORPS KÖRPER CUERPO	PA6.6 30%FG														
GHIERA RING RING ZWINGE CONTERA	PA6.6 30%FG														
CONNETTORE CONNECTOR CONNEXTEUR VERBINDER CONECTOR	4 VIE 4 VIE 4 VIE 4 VIE 4 VIE														
TENSIONE DI ALIMENTAZIONE VOLTAGE TENSION SPANNUNG TENSIÓN	12/24 Vdc $\pm 10\%$ - 90/240 Vac $\pm 10\%$														
SERVIZIO SERVICE SERVICE BETRIEBSART FUNCIONAMIENTO	∞														
CORRENTE NOMINALE CURRENT CONSOMMATION DE COURANT STROMAUFNAHME CONSUMO DE CORRIENTE	<table border="1"> <thead> <tr> <th></th> <th>12 Vdc</th> <th>24 Vdc</th> <th>12 Vac</th> <th>24 Vac</th> <th>90 Vac</th> <th>240Vac</th> </tr> </thead> <tbody> <tr> <td>mA</td> <td>10</td> <td>10</td> <td>20</td> <td>25</td> <td>10</td> <td>20</td> </tr> </tbody> </table>		12 Vdc	24 Vdc	12 Vac	24 Vac	90 Vac	240Vac	mA	10	10	20	25	10	20
	12 Vdc	24 Vdc	12 Vac	24 Vac	90 Vac	240Vac									
mA	10	10	20	25	10	20									
RESA ACUSTICA SOUND OUTPUT RENDEMENT ACOUSTIQUE SOUND OUTPUT SALIDA DE SONIDO	<table border="1"> <thead> <tr> <th></th> <th>12 Vdc</th> <th>24 Vdc</th> <th>12 Vac</th> <th>24 Vac</th> <th>90 Vac</th> <th>240Vac</th> </tr> </thead> <tbody> <tr> <td>dB(A) 1m</td> <td>70</td> <td>70</td> <td>70</td> <td>70</td> <td>70</td> <td>70</td> </tr> </tbody> </table>		12 Vdc	24 Vdc	12 Vac	24 Vac	90 Vac	240Vac	dB(A) 1m	70	70	70	70	70	70
	12 Vdc	24 Vdc	12 Vac	24 Vac	90 Vac	240Vac									
dB(A) 1m	70	70	70	70	70	70									
MODALITA' SUONO SOUND TYPE TONALITE' ACOUSTIQUE SOUND TYPE TIPO DE SONIDO	Suono continuo <i>Continuous sound</i> Son continu Dauernde Tonfolge Sonido fijo														
GRADO IP IP RATING DEGRE IP SCHUTZART GRADO IP	IP65														

P40 A JUNIOR Piezoelectric Sounder



TEMPERATURA DI FUNZIONAMENTO

OPERATING TEMPERATURE
TEMPERATURE DE SERVICE
BETRIEBSTEMPERATUR
TEMPERATURA DE FUNCIONAMIENTO

-30°C+50°C

VIBRAZIONI

VIBRATIONS
VIBRATIONS
VIBRATIONEN
VIBRACIONES

CEI 60068-2-6 SINE

CERTIFICAZIONI, OMOLOGAZIONI

CERTIFICATIONS, APPROVALS
CERTIFICACIONES,
HOMOLOGATIONS
PRODUKTZERTIFIKATE,
ZULASSUNGEN
CERTIFICADOS, HOMOLOGACIONES

CE, UKCA

FISSAGGIO

MOUNTING
FIXATION
FIXIERUNG
FIJACIÓN

Ghiera

Ring
Ring
Zwinge
Contera

DISEGNO

TECHNICAL DRAWING
DESSIN
TECHNISCHE ZEICHNUNG
DIBUJO TECNICO

