

# Water-Proof Video Inspection Camera 3.5"



## Features

IP68 protection  
180 degree rotating function  
Supports micro SD card up to 32G  
Supports snap shots and videos recording  
Can be extended with many different camera (VGA) probe accessories

## Specification

Camera diameter	8.0 ± 1.0 mm
Camera light source	White LEDs x 4pcs
Camera resolution	640 X 480 Pixels
Camera field of view	54°
Camera depth of field	3-6cm
Display resolution	320 x 240 Pixels
Display size	3.5"
Display rotating	180°
IP coverage	IP68 (Main unit) IP67 (Camera head & Probe)
Power supply	AA 1.5V batteries x 4pcs
Probe diameter	6.5mm+/-2mm
Probe length	100cm
Operating temperature	0 to 45°C
Storage temperature	-10 to 50°C
Zoom	Digital 4 times
Minimum bending radius	4.5cm
Power consumption	Max 500mA
Sensitivity	1.8V (Lux,sec)
Color mosaic	RGB Bayer pattern
White comparison	Automatic
Exposure to light	Automatic
Handler end AVI port	NTSC & PAL signal out
Total length of device	111.0 ± 2.0cm
Metal tube length	88.0 ± 2.0 cm

## Accessories

Camera probe  
Magnet  
Hook  
Mirror  
Storage case  
USB cable  
Operating manual

**Art. Nr.**  
**RND 355-00008**

