


# Mains Cable



## Specification

Connector A	Type F (CEE 7/7)
Connector B	IEC 60320 C13
Connector Orientation	Straight/Angled
Cross-Section	0.75 mm <sup>2</sup>
Current Rating	16 A
Jacket Colour	White
Jacket Material	PVC
Length (L)	1.8 m
Voltage Rating Max.	250 V

### Notes:

- 1.Cable:H05VV-F 3G0.75<sup>2</sup>mm Jacket  $\varnothing$ 6.5±0.1 Conductor 24\*0.198
- 2.Mark: <VDE> H05VV-F 3G0.75mm<sup>2</sup>
- 3.Test:Hi-pot: Inner Voltage AC2500V/1S , External Voltage AC4500V/1S  
current leakage 1mA, insulation resistance no less than 50M  $\Omega$ , no strike out;

Art. Nr.  
RND 465-00925

## Product Range

Product name	Model specification	Remarks
RND 465-00924	H05VV-F 3G 0.75mm <sup>2</sup> 1.8M	Black
RND 465-00925	H05VV-F 3G 0.75mm <sup>2</sup> 1.8M	White
RND 465-00926	H05VV-F 3G 1.0mm <sup>2</sup> 2.5M	Black
RND 465-00927	H05VV-F 3G 1.0mm <sup>2</sup> 2.5M	White
RND 465-00928	H05VV-F 3G 1.0mm <sup>2</sup> 5.0M	White