

# ESD Epoxy Coated Tweezers

## Curved/Fine, 120 mm



### Specification

- Low carbon austenitic steel (Material number 1.4435, DIN X2CrNiMo18-14-3, AISI number 316L)
- Contains from 16.5 to 18.5 wt% chromium and has important quantities of nickel and molybdenum as additional alloying elements
- Non-magnetizable (80%)
- Good corrosion resistance to most chemicals, salts and acids
- Generally used where corrosion resistance and toughness are primary requirements
- Typical applications include tweezers for the electronic industry, watch-makers, jewelers and laboratory and medical applications in moderately aggressive chemical environments



### Composition

Component	Wt.%	Component	Wt.%	Component	Wt.%
C	≤0.03	Si	≤1.0	Mn	≤2.0
P	≤0.045	S	≤0.03	Cr	17.0-19.0
Mo	2.5-3.0	Ni	12.5-15.0		

### Mechanical Properties

State	annealed
Density	8.0 g/cm <sup>3</sup>
Hardness HB30	≤ 215
Hardness Rockwell B	79
Tensile strength, ultimate	500-700 MPa
Tensile strength, yield	290
0.2% Yield stress	≥ 200 MPa
Elongation, break	40%
Modulus of elasticity	200 GPa

### Thermal Properties

Coef. of lin. therm expansion	16.0 E-6/°C	20°C-100°C
Coef. of lin. therm expansion	17.0 E-6/°C	20°C-300°C
Specific heat capacity	0.50 J/(g·K)	
Thermal conductivity	15 W/(m.K)	
Continuous use temperature	350°C	
Max service temperature, air	925°C	

### Electrical Properties

Resistivity	0.75 E-4 Ohm.cm
-------------	-----------------

# Economy Tweezers, Curved/Fine, 120 mm



## Product Dimensions

Product OAL (mm - in)	120.00 - 4.724
Product width (mm - in)	10.00 - 0.394
Product height (mm - in)	10.00 - 0.394
Tip thickness A (mm - in)	0.15 - 0.006
Tip width B (mm - in)	0.10 - 0.004

## Art. Nr.

RND 550-00332