

## FEATURES:

Precision wound Nichrome element

Rapid heat-up time (approx. 90 seconds)

Instant heat recovery after soldering

Ventilated neoprene finger grip ensures operator comfort, even under the most demanding production conditions

Fitted with 1.8 metres of heat-resistant silicone mains cable

Supplied with 1.6 mm iron-plated bit

Bit changes are accomplished by simply unscrewing the barrel cover

## SPECIFICATION:

Power	25 W
Soldering temperature	...+430 °C
Voltage	230 VAC



## Art. Nr.

RND 560-00158