

## Features


- Stainless Steel fittings are known for their excellent corrosion resistance, making them suitable for various applications, especially in environments where exposure to moisture or harsh substances is common
- The material's strength and ability to withstand pressure, temperature variations, and mechanical stress
- Stainless steel fittings have smooth surfaces that are easy to clean and maintain



## Specification

Material	Stainless Steel
Medium	Air, Water
Temperature	- 20 ° C ~ 80 ° C
Thread	BSPT
Tolerance	Up to 10 mm and $\pm 0.1$ mm from 12 ~ 14 mm
Burst Pressure	Must not exceed 30 bar

## Product Range & Drawing



Part Number	$\phi D1$ (mm)	$\phi D2$ (mm)	L1 (mm)	L2 (mm)	H (mm)	T	S (mm)
RND 425-00205	11.6	6	48	24	7.5	R 1/8	10
RND 425-00206	11.6	6	48	26	9.5	R 1/4	14
RND 425-00207	13.5	8	51	24.5	7.5	R 1/8	12
RND 425-00208	13.5	8	51	26.5	9.5	R 1/4	14
RND 425-00209	13.5	8	51	27.5	10.5	R 3/8	17
RND 425-00210	15.5	10	56.5	29	9.5	R 1/4	14
RND 425-00211	15.5	10	56.5	30	10.5	R 3/8	17
RND 425-00212	15.5	10	56.5	33	13.5	R 1/2	21
RND 425-00213	17.8	12	61	30	9.5	R 1/4	17
RND 425-00214	17.8	12	61	31	10.5	R 3/8	17
RND 425-00215	17.8	12	61	34	13.5	R 1/2	21