

# Polyester/Cellulose Wipes



## Description

Polyester/Cellulose is a hydroentangled 45% Polyester and 55% Cellulose wiper designed for applications that require the unique combination of superior strength and exceptional sorbency. This wiper is a perfect wiping material for spill control and general purpose wiping.

Image shown for illustration purposes only.

## Features

- Made of hydroentangled 45% Polyester and 55% Cellulose
- Combines the strength of polyester with the absorbency of long cellulose fibres
- Cleanroom processed and packaged to reduce particles
- Smooth, highly sorbent and durable
- Works well with IPA and other solvents

## Applications

- Recommended for use in class ISO3-6 cleanroom environment
- General purpose wiping and polishing of surface areas, including optics
- Excellent for use in Pharmaceutical, Biotech & medical device manufacturing markets
- Available in various sizes and packaging configurations
- Available sterile by Gamma Irradiation



## Releasable Particles

LPC (>0.5um) (IEST-RP-CC 004.3-orbital shake mtd)	82.42 x 10 <sup>6</sup> particles/m <sup>2</sup>
APC (Helmke Drum Test @10rpm); >0.5um (IES-RP-CC003.2)	300 counts/pc/cfm -9" x 9" 5.67 x 10 <sup>3</sup> counts/m <sup>2</sup> /cfm

## FTIR

Ion Content  
(IEST-RP-CC 004.3, Thorough Extraction Method)

ION Content (IEST-RP-CC 004.3, short term extraction)	
Sodium (Na)	0.0012mg/g
Potassium (K)	ND
Magnesium (Mg)	ND
Calcium (Ca)	ND
Chloride (Cl)	0.0500mg/g
Sulphate (SO4)	0.0660mg/g

## Contamination Characteristics

Nonvolatile Residue, NVR (IEST-RP-CC 004.3, Analysis for Unspecified Extractable Matter)	
IPA Extractant	0.431mg/g
DIW Extractant	0.091mg/g

## Performance Characteristics

Basis Weight	68gsm
Thickness (micrometer)	0.30mm
Absorbency (IEST-RP-CC 004.3)	
Sorptive capacity	288 ml/m <sup>2</sup>
Rate (Drop Disappearance mtd.)	< 0.8 sec

---

Product code	Description	QTY	Size
RND 600-00127	Polyester/Cellulose Wipes	Pack of 100	9"x9"
RND 600-00128	Polyester/Cellulose Wipes	Pack of 300	9"x9"