

# SEM Electronic Horn



RND 430-00104 (24V)



RND 430-00105 (240V)


Dispositivo di segnalazione acustica.

*Acoustic warning device.*

*Dispositif de signalisation acoustique.*

*Akustikmodul.*

*Zumbador.*

<b>CUPOLA</b> DOME DOME HAUBE CÚPULA	PC						
<b>BASE</b> BASE BASE SOCKET BASE	PC/ABS						
<b>GUARNIZIONE</b> GASKET JOINT DICHTUNG JUNTA	O-Ring EPDM						
<b>COLORI DISPONIBILI</b> AVAILABLE COLOURS COULEURS DISPONIBLES VERFÜGBARE FARBEN COLORES DISPONIBLES							
<b>VOLTAGGIO</b> VOLTAGE TENSION SPANNUNG TENSIÓN	24Vdc - 240Vac						
<b>SERVIZIO</b> OPERATION FONCTIONNEMENT BETRIEBSART FUNCIONAMIENTO	T: ON = 1min. OFF = 10min.						
<b>CORRENTE NOMINALE</b> CURRENT CONSUMPTION CONSOMMATION DE COURANT STROMAUFNAHME CONSUMO DE CORRIENTE	<table border="1"> <thead> <tr> <th></th> <th>24Vdc</th> <th>240Vac</th> </tr> </thead> <tbody> <tr> <td>mA (Max)</td> <td>40</td> <td>35</td> </tr> </tbody> </table>		24Vdc	240Vac	mA (Max)	40	35
	24Vdc	240Vac					
mA (Max)	40	35					
<b>RESA ACUSTICA</b> ACOUSTIC OUTPUT RENDEMENT ACOUSTIQUE SCHALLLEISTUNGSPEGEL SALIDA ACUSTICA	<table border="1"> <thead> <tr> <th></th> <th>24Vdc</th> <th>240Vac</th> </tr> </thead> <tbody> <tr> <td>dB(A)1m</td> <td>96</td> <td>95</td> </tr> </tbody> </table>		24Vdc	240Vac	dB(A)1m	96	95
	24Vdc	240Vac					
dB(A)1m	96	95					
<b>GRADO IP</b> IP RATING DEGRE IP SCHUTZART GRADO IP	IP43						

# SEM Electronic Horn



<b>TEMPERATURA DI FUNZIONAMENTO</b> <i>OPERATING TEMPERATURE TEMPERATURE DE SERVICE BETRIEBSTEMPERATUR TEMPERATURA DE FUNCIONAMIENTO</i>	-30°C+50°C
<b>CERTIFICAZIONI, OMOLOGAZIONI</b> <i>CERTIFICATIONS, APPROVALS CERTIFICACIONES, HOMOLOGATIONS PRODUKTZERTIFIKATE, ZULASSUNGEN CERTIFICADOS, HOMOLOGACIONES</i>	CE, UKCA
<b>FISSAGGIO</b> <i>MOUNTING FIXATION FIXIERUNG FIJACIÓN</i>	<b>Viti</b> <i>Screws Vis Schrauben Tornillos</i>
<b>DISEGNO</b> <i>TECHNICAL DRAWING DESSIN TECHNISCHE ZEICHNUNG DIBUJO TECNICO</i>	<p>Technical drawing of the SEM Electronic Horn. The drawing shows two views: a front view and a side view. The front view shows a horn with a diameter of 76 mm at the top. The height of the horn is 99 mm. The total height of the horn, including the mounting base, is 204 mm. The width of the horn at the base is 58 mm. The side view shows the horn's profile and a mounting hole with a diameter of 5 mm. The width of the horn at the base is 79 mm.</p>