

Medium Wall Heat-Shrink Tubing

Features

- Medium-wall tubing
- Good environmental protection
- Good electrical and mechanical performance
- Ideal for low voltage applications
- UV resistant
- Recommended to applications for light cable and wire harnesses that require waterproofing, protection, and sealing of connectors components within the tubing.



Specification

Material	Polyolefin, Matt Surface
Shrink Ratio	4:1
Shrink Temperature	120 °C
Service Temperature Range	-55 ... 110°C
Colour	Black
Dielectric Strength	>20 kV

Product Range

Type	As supplied: inside diameter in mm (min.)	After recovery: inside diameter in mm (max.)	After recovery: wall thickness in mm (min.)	Standard length in m
RND 465-01215	8.0	2.0	1.6	1.22
RND 465-01216	12.0	3.0	2.0	1.22
RND 465-01217	16.0	5.0	2.2	1.22
RND 465-01218	22.0	6.0	2.4	1.22
RND 465-01219	28.0	6.0	2.5	1.22
RND 465-01221	45.0	12.0	2.6	1.22
RND 465-01222	55.0	16.0	2.7	1.22
RND 465-01223	65.0	19.0	2.9	1.22
RND 465-01224	75.0	22.0	3.0	1.22
RND 465-01225	85.0	25.0	3.0	1.22
RND 465-01226	95.0	25.0	3.0	1.22