

# Neodymium Countersink Magnet



## Features

- High coercivity (Hci) to resist demagnetisation
- Strongest magnetic performance
- Lightweight and compact because of the high energy density of the magnet material
- Can be used in computers, automobiles, electric machinery, offices, schools, homes, warehouses and restaurants



## Specification

Material	Neodymium Magnet				
Magnet Type	Countersink				
Grade	N35				
Coating	Ni-Cu-Ni				
Magnetized Direction	Through thickness				
Part No.	Outer Diameter	Diameter 1	Diameter 2	Thickness	Net weight (g/pcs)
RND 610-00906	10 mm	7 mm	4 mm	3 mm	1.2
RND 610-00907	15 mm	10.7 mm	5.3 mm	4 mm	3.79
RND 610-00908	16 mm	10 mm	4.5 mm	5.5 mm	6.5
RND 610-00909	20 mm	10 mm	5.2 mm	5.5 mm	11.08