


Multilayer Capacitors, SMD

Multilayer Ceramic Capacitors, 0805, NPO, Auto-



FEATURES:

Automotive Capacitors

With lead-free termination (pure Tin)

Meets AEC-Q200 requirements

SPECIFICATION:

Construction form	0805
Ceramic type	NPO
Temperature range	-55...+125 °C
Length	2.0 mm
Width	1.25 mm

PRODUCT RANGE:

Art. Nr.	Capacitance	Rated voltage	Capacitance tolerance	Dimensions L x H x W	Height
RND 150MT21N2R2C500	2.2 pF	50 VDC	±0.25 pF	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N2R2C101	2.2 pF	100 VDC	±0.25 pF	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N3R3C500	3.3 pF	50 VDC	±0.25 pF	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N4R7C500	4.7 pF	50 VDC	±0.25 pF	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N4R7C101	4.7 pF	100 VDC	±0.25 pF	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N6R8C500	6.8 pF	50 VDC	±0.25 pF	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N6R8C101	6.8 pF	100 VDC	±0.25 pF	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N100F250	10 pF	25 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N100F500	10 pF	50 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N220F100	15 pF	10 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N150F500	15 pF	50 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N150F101	15 pF	100 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N220F250	22 pF	25 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N220F500	22 pF	50 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N330F500	33 pF	50 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N330F101	33 pF	100 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N470F160	47 pF	16 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N470F500	47 pF	50 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N680F100	68 pF	10 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N680F500	68 pF	50 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N101F250	100 pF	25 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N101F500	100 pF	50 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N101F101	100 pF	100 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N221F250	220 pF	25 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N221F500	220 pF	50 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N221F101	220 pF	100 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N331F500	330 pF	50 VDC	±1%	2.0 x 0.6 x 1.25 mm	0.6 mm
RND 150MT21N471F101	470 pF	100 VDC	±1%	2.0 x 0.8 x 1.25 mm	0.8 mm

Art. Nr.	Capacitance	Rated voltage	Capacitance tolerance	Dimensions L x H x W	Height
RND 150MT21N102F500	1.0 nF	50 VDC	±1%	2.0 x 0.8 x 1.25 mm	0.8 mm
