Stripping tool



FEATURES:

Coaxial stripping tool with three adjustable cutters

Tool is preseted for RG58/59/62/6 cable types

Total stripping distance 10 or 12 mm


With streamlined design, no need replacing cassette and adjusting V-block Use the built-in hex wrench to align the socket and adjust the blade




SPECIFICATION:


Stripped values A	10 mm	
Stripped values B	12 mm	
Colour	black	
Length	108 mm	
Weight	74 g	











INSTRUCTIONS:

Stripping length is set to 12 mm if you want to strip other lengths, you may adjust the blade's position.

Blade's depth are preset .usually no adjustment is needed but if you find the stripper doesn't strip your cable well, then you may use the hex wrench, which is installed on the bottom of the tool to adjust the blades' depth.

Stripping cable:

- **1.** The stripper is designed for stripping cables without any adjustment of V-block.
- **2.** Press the knurled portion on the upper jaw to open the stripper's jaws.
- 3. Insert the cable you want to strip through the V-block until the cable reaches the V-shaped cable guide. Then release the upper jaw to close the jaws
- **4.** Insert your index finger into the stripper's finger ring, turn the stripper clockwise 3-5 times. The cable's insulation is cut while you turn the stripper
- 5. Open the jaws and remove the cable. Pull away the outer jacket and dielectric to expose the inner conductor

Art. Nr.

RND 550-00175