

AC POWER SUPPLY SPECIFICATION



MODEL NO - RND 320-00054

INPUT

INPUT VOLTAGE	100 to 240 VAC
INPUT FREQUENCY	60/ 50 Hz
PROTECTIVE DEVICE	Fuse, 1A 250V
NO LOAD POWER CONSUMPTION	<0.1W
INPUT FULL LOAD CURRENT (at 100Vac)	0.35A

OUTPUT

OUTPUT VOLTAGE	12V dc
OUTPUT CURRENT	1500mA

OVERALL PERFORMANCE

TOTAL OUTPUT POWER	18 W Max
EFFICIENCY	Comply with ErP; level VI

PROTECTION

■ OVER CURRENT PROTECTION	■ SHORT CIRCUIT PROTECTION
■ OVERVOLTAGE PROTECTION	■ L.P.S (Limits for power source)
■ OVER POWER PROTECTION	□ AUTOMATIC THERMAL PROTECTION

HI-POT

INPUT TO OUTPUT	3000Vac 5 mA 50 Hz
INPUT TO CASE	3000Vac 5 mA 5Hz
OUTPUT TO CASE	500 Vac 5 mA 50Hz
ISOLATION RESISTANCE	100 M Ohms I/P-O/P I/P/Enclosure
APPLIANCE	Class II

ENVIRONMENTAL

OPERATING TEMPERATURE	0 °C to 40 °C
STORGE TEMPERATURE	-20 °C to 60 °C
OPERATING HUMIDITY	20%-85% RH. NON-CONDENSING
STORGE HUMIDITY	10%-90% RH. NON-CONDENSING

APPROVAL

SAFETY STANDARDS	EN62368-1:2014+A11:2017
EMC	EN 61204-3:2000


RELIABILITY

MTBF	30000 Hours min
BURN-IN	4 Hours 25°C, full load, 220Vac, 50Hz


MECHANICAL SPECIFICATION

DIMENSION	82 mm(L)* 51.6 mm(W)* 35.9 mm(H) (excluded plug) 82 mm(L)* 51.6 mm(W)* 73.2 mm(H) (included plug)
WEIGHT	130g (excluding packaging)
INPUT PLUG	Direct plug-in; EU type
OUTPUT CABLE	1.8m Black and white wires,
OUTPUT CONNECTOR	Plug G: 5.5x2.5/12

OTHER SPECIFICATIONS

<p>TIME SEQUENCE</p>	<p>Time sequence should be satisfied to power ON/OFF, restart in power failure AC switch at ON/OFF</p> 
<p>DROP TEST</p>	<p>Test condition: 6 face, each face 1 time 70 cm, on the 5mm wooden board. RESULT: Without opening of case and crack, etc. electric characteristic shall be satisfied light crack after test is acceptable.</p>
<p>ENVIRONMENTAL TEST</p>	<p>LOW TEMPERATURE STORAGE TEST Keep on -30°C(Packing) for 168 hours, and check the action after 3 hours in 25°C. RESULT: All normal function and meet specification.</p> <p>HIGH TEMPERATURE STORAGE TEST Keep on +70°C(Packing) for 168 hours, and check the action after 3 hours in 25°C. RESULT: All normal function and meet specification.</p> <p>HIGH HUMIDITY STORAGE TEST Keep on +45°C, 95%RH (Packing) for 168 hours, and check the action after 3 hour in 25°C. RESULT: All normal function and meet specification.</p> <p>TEMPERATURE CYCLE TEST Keep on -45°C(Packing) for 1 hour, then keep on +85°C(Packing) for 1 hour Repeat this cycle until 10 cycle, check the action after an hour in 25°C. RESULT: All normal function and meet specification.</p>

Appearance



贴片2TP-3R15U

