

## FEATURES:

- Precision wound Nichrome element
- Rapid heat-up time (approx. 90 seconds)
- Instant heat recovery after soldering
- Ventilated neoprene finger grip ensures operator comfort, even under the most demanding production conditions
- Fitted with 1.8 metres of heat-resistant silicone mains cable
- Supplied with 1.6 mm iron-plated bit
- Bit changes are accomplished by simply unscrewing the barrel cover

## SPECIFICATION:

Power	25 W
Soldering Temperature max.	430 °C
Plug version	EU
Voltage	230 V



# Soldering Tips for RND 560-00158

## Features

- -
- 7
- 0
- For universal soldering jobs



## Specification

Power Rating	25 W
Soldering Tip Shape	Pencil Point
Tip Width	RND 560-00256 - 0.8 mm RND 560-00257 - 1.6 mm RND 560-00257 - 3.2 mm
Suitable for	RND 560-00158 Soldering Iron
Tip Length	51 mm