Static Shielding Bag -Gripseal



Description

An anti-static shielding ziplock/gripseal bag providing full protection against ESD. This bag is designed to give ultimate protection against static damage to electronic components and devices whilst being handled in storage and during transportation.

Features

Seal

- Metal "Faraday cage" layer shields products from electric energy inside and prevents static build-up
- · Four layer protection guards against charges inside and out
- \cdot Semi transparent for easy content identification
- \cdot Surface resistance of $10^6\text{-}10^{10}\Omega/\text{sq}$
- Conforms to EIA 625, EIA 541, ANSI/ESD S-20.20
- Custom sizes and print available on request
- Suitable for packing electronic products which are sensitive
- to static, eg PCBs, electronic components etc

.....





Static Shielding Bag -Gripseal



Test Conditions

The following results were taken under the following environmental test conditions: Temperature: $23^{\circ}C$ / Humidity: 12% RH

Technical Parameters

Item	Test Standard	Result	
Film Thickness	Micron Meter	3mils 75 micron	
Metal Layer Optical Transmission	ASTM D1003 (TOBIAS)	40% +/- 5% optical density	
Surface Resistivity	STM 11.11	>10 ⁶ Ω <10 ¹⁰ Ω/sq	
Time For Static Removal	FTMS 101B Method 4046 - 5000-0V	<.0.03 Sec	
Static Shielding - Energy Penetration	ESD-STM-11.31 @12% R.H.	<10 nJ	
Static Shielding - Capacitive Probe	EIA 541 Appendix E	<10V	
Friction Static	E1A541 Appendix C Avg.	Triboelectric nanocoulombs Quartz +0.01 Tefion -0.09	
Tensile Strength	ASTM D882-91, Method A	MD 6530 psi TD 5800 psi	
Tear Initiation	ASTM D1004 -94-Notched	MD 2.5 lbs./in TD 2.0 lbs	
Puncture Resistance	ASTM D3420	>10 psi	
Tear Resistance	ASTM D882	>8 psi	
Burst Strength	FTMS 101 C Method 2065.1	50 psi nominal	
Heat Seal Temperature	-	250 - 375 °F	
Heat Seal Pressure	-	30-70 PSI	
Breaking Elongation Rate	ASTM D882-91 Method A	MD 80% TD 85%	
Appearance	GB/96-04-10	No delamination, burst seal, wrinkle, warp, break, foreign particle adherence, air bubble beyond sealing ≤3mm	

Product Code	Size (inches)	Size (mm)	Additional Notes
RND 600-00044	3 x 5	76 x 127	Pack of 100
RND 600-00045	4 x 6	102 x 152	Pack of 100
RND 600-00046	5x8	127 x 203	Pack of 100
RND 600-00047	6 x 10	152 x 254	Pack of 100
RND 600-00048	8 x 10	203 x 254	Pack of 100
RND 600-00049	8 x 12	203 x 305	Pack of 100
RND 600-00050	10 x 12	254 x 305	Pack of 100
RND 600-00051	6 x 8	152 x 203	Pack of 100