### **Features**

## **Power Module**

- High power density (L\*W\*H = 12.19\*12.19\*3.75)
- Wide operating temperature -40°C to +107°C at full load
- Efficiency up to 99%, no need for heatsinks
- 6-sided shielding
- Thermally and EMI enhanced 25 pin LGA package
- **Compact DOSA-compatible footprint**
- Low profile

#### **Description**

The RPM-1.0 series is a 1A non-isolated switching regulator power module with a full set of features including adjustable output, sequencing, soft-start control, on/off control, and power good signals. The ultra-compact module has a profile of only 3.75mm, but with an efficiency of up to 99%, the device can operate at full load in ambient temperatures as high as +107°C without forced air cooling. The package is complete with 6-sided shielding for optimal EMC performance and excellent heat management.



### **RPM-1.0**

## 1 Amp **Single Output**



Selection Guide									
Part Number	Input Voltage Range [VDC]	Output Voltage [VDC]	Vout Adjust Range [VDC]	Output Current max. [A]	Efficiency typ. [%]	Max. Capacitive Load <sup>(1)</sup> [μF]			
RPM3.3-1.0 (2)	3 - 17	3.3	0.9 - 6.0	1	94 - 99	800			
RPM5.0-1.0 (2)	3 - 17	5	0.9 - 6.0	1	92 - 99	800			



Note1: Max. Cap Load is tested at nominal input and full resistive load








EN55032 compliant

### **Model Numbering**



#### Notes:

Note2: add suffix "-CT" for tube packaging for more details refer to "PACKAGING INFORMATION" without suffix, standard tape and reel packaging

#### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Parameter		Condition		Min.	Тур.	Max.
Internal Input Filt	ter					capacito
Input Voltage	Buck mode		3.3Vout 5Vout	3.35VDC 5.05VDC	12VDC	17VDC
Range	100% duty cycle mode (3)	Vout= Vin - Vdrop	3.3Vout 5Vout	3VDC		3.35VDC 5.05VDC
Absolute Maximi	um Input Voltage					20VDC
Undervoltage Lo	ckout (UVLO)	DC-DC ON DC-DC OFF	2.6VDC 2.8VDC	2.7VDC 2.9VDC	2.8VDC 3.0VDC	
Input Current		nom. Vin= 12VDC	3.3Vout 5Vout		0.3A 0.45A	
Quiescent Curre	nt				30μΑ	
Internal Power D	issipation		3.3Vout 5Vout			0.27W 0.32W





### **Series**

#### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Parameter	Condition	Min.	Тур.	Max.	
Output Voltage Trimming (4)		0.9VDC		6VDC	
Minimum Dropout Voltage (Vdrop) (5)	Vin min. = Vdrop + Vout		50mV/A		
Minimum Load		0%			
Start-up Time	without using soft start function/ power up		1.6ms		
Start-up fille	using CTRL function		1.5ms		
Rise-time			1.4ms		
ON/OFF CTRL	DC-DC ON		Оре	en or 0.9V <v<sub>CTRL<vin< td=""></vin<></v<sub>	
OWOIT CIRL	DC-DC OFF	Short or -0.3V <v<sub>CTRL&lt;0.45VDC</v<sub>			
Input Current of CTRL Pin	DC-DC OFF		1.2µA		
Standby Current	DC-DC OFF		15µA		
Internal Operating Frequency			1.25MHz		
Output Ripple and Noise (6)	20MHz BW, 800hm @ 100MHz		60mVp-p		
Absolute Maximum Capacitive Load	below 1 second start up + $C_{ss} = 3700nF$			42000µF	
Absolute Maximum Capacitive Load	below 1 second start up without softstart mode			800µF	

#### Notes:


Note3: As input approaches output voltage set point, device enters 100% duty cycle mode. in 100% duty cycle mode, Vout equals Vin minus dropout voltage (see Dropout vs. Load graph)

Note4: For more detailed information, please refer to trim table or calculation on page RPM-3

Note5: Required dropout voltage per 1A output current to be within accuracy (see Dropout vs. Load graph)

Note6: Measurements are made with a 22µF MLCC across output (low ESR)

#### Efficiency vs. Load






**Series** 

#### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

#### **OUTPUT VOLTAGE TRIMMING**

The RPM series offers the feature of trimming the output voltage over a range between 0.9V and 6V by using external trim resistors. The values for trim resistors shown in trim tables below are according to standard E96 values; therefore, the specified voltage may slightly vary.



Vout<sub>nom</sub> = nominal output voltage [VDC] Vout<sub>set</sub> = trimmed output voltage [VDC]

 $R_1, R_2, R_3 = internal resistors$  $[\Omega]$ 

[VDC]
$[\Omega]$
$[\Omega]$

Vout <sub>nom</sub>	R <sub>1</sub>	R <sub>2</sub>	R <sub>3</sub>	V <sub>ref</sub>
3.3VDC	376kΩ	1kΩ	471kΩ	0.81VDC
5VDC	344kΩ	1 K 2 2	431kΩ	0.61700

#### Calculation:

$$\mathbf{R}_{\mathbf{up}} = \begin{bmatrix} \frac{\mathbf{R}_1}{\mathbf{Vout}_{\mathsf{set}} - \mathbf{V}_{\mathsf{norm}}} \end{bmatrix} - \mathbf{R}_2$$

$$\mathbf{R_{down}} = \begin{bmatrix} \frac{(Vout_{set} - V_{ref}) \times R_3}{Vout_{nom} - Vout_{set}} \end{bmatrix}$$

#### Practical Example RPM3.3-1.0:

$$\mathbf{R}_{up} = \begin{bmatrix} 376k \\ 4.3 - 3.3 \end{bmatrix} - 1k = 375k\Omega$$

 $R_{un}$  according to E96  $\approx 374k\Omega$ 

$$\mathbf{R}_{\text{down}} = \left[ \frac{(1.8 - 0.81) \times 471 \text{k}}{3.3 - 1.8} \right] = \underline{\mathbf{311k\Omega}}$$

 $\mathbf{R}_{\text{down}}$  according to E96  $\approx 309 \text{k}\Omega$ 

#### RPM3.3-1.0

#### Trim up

Vout <sub>set</sub> =	3.5	3.7	3.9	4.1	4.3	4.5	4.7	5.0	5.5	6.0	[VDC]
R <sub>up</sub> (E96) ≈	1M87	931k	619k	464k	374k	309k	267k	221k	169k	137k	[Ω]

#### Trim down

Vout <sub>set</sub> =	3.0	2.7	2.5	2.2	2.0	1.8	1.5	1.2	1.0	0.9	[VDC]
R <sub>down</sub> (E96) ≈	3M40	1M47	1M	590k	432k	309k	182k	86k6	39k2	17k4	$[\Omega]$

#### RPM5.0-1.0

#### Trim up

Vout <sub>set</sub> =	5.1	5.2	5.3	5.4	5.5	5.6	5.7	5.8	5.9	6.0	[VDC]
$R_{up}$ (E96) $\approx$	2M21	1M33	976k	750k	619k	523k	453k	402k	357k	324k	$[\Omega]$

#### Trim down


Vout <sub>set</sub> =	4.5	4.0	3.5	3.3	2.5	1.8	1.5	1.2	1.0	0.9	[VDC]
$R_{down}$ (E96) $\approx$	3M16	1M37	768k	634k	294k	133k	84k5	44k2	20k5	9k53	[Ω]



**Series** 

#### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

#### **REMOTE SENSE**



The output voltage can be adjusted via the trim and sense functions.

The maximum output voltage from Trim and Sense function combined is 5.5VDC. Derating may be required when using Trim and/or sense functions.

 $\mathbf{RW_1}$  ... wire losses +  $\mathbf{R_{up}}$  ... trim up resistor  $\mathbf{R_{down}}$  ... trim down resistor

REGULATIONS								
Parameter	Condition	Value						
Output Accuracy		±3.0% max.						
Line Regulation	low line to high line, full load	0.25% typ. / ±3.0% max.						
Load Regulation	0% to 100% load	0.5% typ. / 3.0% max.						
Soft-Start Time		refer to soft-start capacitor calculation						
	100% - 10% load step	200mV max.						
Transient Deepense	recovery time	6ms typ.						
Transient Response	25% load step change	150mV max.						
	recovery time	500μs typ.						

#### **Sequencing Multiple Modules**

The SEQ pin can be used to program the rising edge of the output voltage. An internal current source charges a soft-start capacitor which is connected from the sequencing pin to GND. The following equation is used to calculate the soft-start capacitor:

 $C_{ss}$  = soft-start capacitor

= sum of all soft-start currents of all sequenced modules

 $t_{ss}$  = required soft-start time

 $\vec{n}$  = number of RPMs

$$\mathbf{C_{ss}} = \frac{\mathsf{t_{ss}} \, \mathsf{x} \, \mathsf{I_{ss}}}{1.25 \mathsf{V}} - \mathsf{n} \, \mathsf{x} \, 3.3 \mathsf{nF}$$

Note: there is a 3.3nF internal soft-start capacitor, and there are different constant current sources in the modules which leads to different preset soft-start times.


	I <sub>ss</sub> [μA]		Preset soft-start time [µs]			
Min.	Тур.	Max.	Min.	Тур.	Max.	
4.5	5.0	5.5	750	825	920	




**Series** 

#### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

To sequence multiple power module start-up times the power good (PGood) pin and the CTRL pin may be used. In below schematic, the RPM(n) starts after RPM(1) reaches its set output voltage and the power good signal is set to high which then enables RPM(n). After RPM(n) reaches its set output voltage, it enables RPM(n+1).



To sequence multiple converters to start at the same time (set output voltage is reached at the same time), the following schematic may be used:





### **Series**

### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

PROTECTIONS									
Parameter	Cond	ition	Value						
Short Circuit Protection (SCP)	50m	ηΩ	constant current mode						
Short Circuit Input Current	without soft-	start mode	75mA typ.						
Over Current Protection (OCP)	with soft-s	tart mode	120%, pulse by pulse current limitation						
Over Temperature Protection (OTP)	case temperature (measured on tc point)	DC-DC OFF DC-DC ON	110°C, auto restart after cool dow 100°C typ						


ENVIRONMENTAL			
Parameter	Condition		Value
Operating Temperature Range (7)	@ natural convection 0.1m/s (refer to derating graph)		-40°C to +105°C
Maximum Case Temperature	measured on tc point (see dimension drawing)		+110°C
Temperature Coefficient	@ +65°C Tamb		0.02%/K
Thermal Impedance (7)	0.1m/s, horizontal (Tcase to Tamb)		8K/W
Operating Altitude	with derating @ natural convection 0.1m/s (refer to altitude vs. load graph)		5000m
Operating Humidity	non-condensing		5% - 95% RH max.
Shock	MIL-STD-810G, Method 516.6, Procedure I		40g, 11ms, saw-tooth, 3 shocks ± per axis 3 axis; unit is operating
	MIL-STD-810G, Method 516.6, Procedure IV		drop on 50mm plywood on concrete 26 times from 1 meter
Temperature Cycling	MIL-STD-883F, Method 1010, Condition A		powered -50°C to +85°C, 300 cycles
Random Vibration	MIL-STD-810G, Method 514.6, Procedure I, Category 24		Category 24 - Figure 514.6E-1 - power spectral density = 0.04g <sup>2</sup> /Hz at 20Hz -1000Hz; -6dB/octave at 1000Hz - 2000Hz; 60 minutes x 3 axis; unit is operating during tests
MTBF	according to MIL-HDBK-217F, G.B. @ full load	+25°C +85°C	2900 x 10 <sup>3</sup> hours 950 x 10 <sup>3</sup> hours

#### Notes:

Note7: tested with a eurocard 160x100mm 70µm copper, 4 layer

#### Derating Graph (7)

(@ chamber and natural convection 0.1m/s)






### **Series**

### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

SAFETY AND CERTIFICATIONS		
Certificate Type (Safety)	Report / File Number	Standard
Audio/video, information and communication technology equipment. Safety requirements	designed to meet	EN62368-1
RoHS 2		RoHS 2011/65/EU
EMC Compliance	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment - emission requirements	with external components (see filter suggestions below)	EN55032, Class A and B


#### EMC filtering suggestion according to EN55032



#### **Component List Class A**

C1	C2 (8)	FB1
10F 05V V7D	10F 051/ V7D	WE ref:
10μF 25V X7R	10μF 25V X7R	742792510

#### EMC filtering suggestion according to EN55032



#### Component List Class B

C1	C2 <sup>(8)</sup>	FB1	FB2	C3	
10uF 25V X7R	10µF 25V X7R	WE ref:	WE ref:	22uF 10V 7XR	
10μι 237 λ/ Ν	Τυμι 230 Α/Τι	742792510	7427932	ΖΖμΙ ΙΟΥ / ΛΝ	

Notes:

Note8: C2 is only required below 10V input voltage

DIMENSION AND PHYSICAL CHARACTERISTICS		
Parameter	Туре	Value
	case	metal
Material	PCB	FR4, (UL94 V-0)
	solder pads	copper with electrolytic nickel-gold
Dimension (LxWxH)		12.19 x 12.19 x 3.75mm
Weight		1.1g typ.
	·	




### **Series**

#### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

#### **Dimension Drawing (mm) Pinning information** Pad # Function Description ±0.2 12.19 ± Positive input voltage with respect to GND. Connect to a A1, A2 Vin Vin plane for enhanced thermal performance Active High: pull to GND to disable the device. C1 CTRL Pull high or leave open to enable the device Positive output voltage. Connect to a Vout plane for 12.19 ±0.5 A5, B5 Vout enhanced thermal performance Connect this pad to the load or directly to Vout. 11.70 11.70 C5 Sense This pad must not be left floating E5 Trim Used to set the output voltage between 0.9V and 6V E2 NC Not connected Used to sequence multiple converters or to set the **Recommended Footprint Details** E1 SEQ startup time. Float if not used **Bottom View Top View** Output power good. High = Vout at set level, low = Vout 25 x □1.0 1.06 below nominal regulation. Maximum sink current is D1 **PGood** 2mA. It has a high impedance output $(100k\Omega$ connected to Vout). Float if not used A3, A4, B1, B2, B3, B4, C2, C3, Negative input voltage. Connect to GND plane(s) for GND enhanced thermal performance В □ □ □ □ D C4, D2, D3, \_ \_ \_ \_ | E D4, D5, E3, E4 П 2 3 2 tc = case temperature measuring point

Pad tolerance= ±0.05mm





### **Series**

### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

PACKAGING INFORMATION		
Parameter	Туре	Value
	tape and reel	330.2 x 330.2 x 30.4mm
Packaging Dimension (LxWxH)	tape and reel (carton)	355.0 x 350.0 x 50.0mm
	tube ("-CT")	530.0 x 30.3 x 19.2mm
Dealessing Opentity	tape and reel	500pcs
Packaging Quantity	tube ("-CT")	30pcs
Tape Width		24mm
Storage Temperature Range		-55°C to +125°C
Storage Humidity	non-condensing	95% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

www.recom-power.com REV.: 3/2019 RPM-9