

Watertight Case with Cubed Foam



Features

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Polyamide pins, corrosion free
- Screen printing and resin label space
- Convoluted foam in the lid and cubed foam in the bottom with pick and pluck system to easily adapt the case to your objects



Specification

IP67 RATING **ATA 300** **MIL SPECS** DEF STAN 81-41
STANAG 4280

External Dimensions	502 x 415 x 246 mm
Internal Dimensions	465 x 335 x 220 mm
Cover Depth - Bottom	40 + 180 mm
Weight	3.96 kg
Temperature Range	-30 ... 90 °C
Capacity	34.27 l
Protection Rating	IP67

Material Specification

Base	Polypropylene Copolymer
Latches	Polyamide
O-Ring	Polymer
Moulding	Injection Moulded

Art. Nr.
RND 600-00302