

Integrity Low Linting Perforated Roll



Features

- Smooth, highly absorbent and durable
- Suitable for use in class 100 cleanrooms
- Large perforated sheet
- Low extractable levels and particle counts
- General equipment wrap & wipe downs
- For use in laboratories, electronic assembly etc.
- Chemically compatible with common cleaning products
- Autoclavable
- 450 wipes with perforated core per roll
- 2 rolls per wrap



Raw Material Data

Fibre content	Mixed Fibre Polyester / Cellulose
Weight (gsm/m ²) ISO 9073-1	65.93 – 72.87
Thickness (mm) ISO 9073-2	0.285 – 0.315
Liquid Absorptive Capacity (%) ISO 9073-6	366.60–448.07
Liquid Absorbency Time (s) ISO 9073-6	2.23 – 2.73
Tensile Strength (N/50mm)	
MD Dry	199.3
CD Dry	55.4
MD Wet	144.8
CD Wet	41.10
ELONGATION (%)	
MD Dry	23.0
CD Dry	87.0
MD Wet	26.0
CD Wet	68.5
Elmdorf tearing resistance CDE (mN)	5933
Particles >0.5 µm/ m ² (x106) IEST-RP-CC004.3	≤ 878
Fibres > 100 µm/ m ² (x106) IEST-RP-CC004.3	≤ 1.05
Non-volatile Residues (g/ m ²) IEST-RP-CC004.3	
DI Water	≤ 0.063
Isopropyl Alcohol	≤ 0.017
METALS AND IONS (µg/ g or ppm) IEST-RP-CC004.3	
Ca ²⁺	≤ 27.8
Mg ²⁺	≤ 16.0
K ⁺	≤ 9.58
Na ⁺	≤ 65.9

PRODUCT CODE	DESCRIPTION	COLOUR	SIZE (mm) (W X L)	PACK SIZE	PACKAGING
RND 600-00330	Low linting perforated roll	White	266 x 380	1 Roll	Polywrap