



## Features

- 
- 
- Output
- Output
- \
- \
- y
- 0
- =
- k
- " yo" ko 8h@ 0 V



Four-channel sequence wave output



Various dynamic waveform outputs



Step	Voltage(V)	Current(A)	Time(s)
1	0.400	0.1500	0.500
2	0.700	0.2500	1.200
3	1.000	0.2500	1.500
4	1.300	0.3000	1.800
5	1.600	0.3500	2.100
6	1.900	0.4000	2.400
7	2.200	0.4500	2.700
8	2.500	0.5000	3.000
9	2.800	0.5500	3.300
10			

Simple LIST sequence setting interface



Export of U disk data

## Specification

Voltage	4x 0 ... 30V
Current	4x 0 ... 5A

### Load Regulation

Voltage	≤ 1 mV
Current	≤ 1 mA

### Setup Regulation

Voltage	1 mV
Current	0.1 mA

### Read Back Resolution

Voltage	1 mV
Current	0.1 mA

### Setup Accuracy (25°C ± 5°C)

Voltage	≤ 0.005% + 2 mV
Current	≤ 0.05% + 1 mA

### Ripple(20-20M)

Voltage	≤ 1 mVrms
Current	≤ 3 mArms

### Temp. Coefficient

Voltage	≤ 100 ppm
Current	≤ 100 ppm

### Read Back Temp. Coefficient

Voltage	≤ 100 ppm
Current	≤ 100 ppm

### Accessories

User manual, Power cord

### Weight and Dimensions

430 mm(W)\*88 mm(H)\*440 mm (D), 16.5 Kg