

# **Power PCB Relay RT1**

- 1 pole 12A/16A, 1 form C (CO) or 1 form A (NO) contact
- **■** DC or AC coil
- 5kV/10mm coil-contact, reinforced insulation
- Ambient temperature 85°C (DC coil)
- WG version: product in accordance to IEC 60335-1
- Reflow version: for THR (Through-Hole Reflow) soldering process

Typical applications

Boiler control, timers, garage door control, POS automation, interface modules




VDE Cert. No. 40007571, cULus E214025, cCSAus 1142018; CQC in preparation

Technical data of approved types on request

10011110011001001010101	,pp. 0 v 0 a 1, p 0 0 0	roquo					
<b>Contact Dat</b>	a		12	2A	16	Α	
Contact arrange	1 form	1 form C (CO) or 1 form A (NO)					
Rated voltage			VAC				
Max. switching	voltage				VAC		
Rated current			12	-, ,	16A		
Limiting continu			12	12A 16A, UL: 20A			
Limiting making							
max. 4s, duty			25		30		
Breaking capac			300		4000		
Contact materia		1.1		)/10, Agl	Vi 90/10 go	old plated	
Frequency of or	peration, with/v	vithou	t load	000/7	20001 1		
DC coil					2000h <sup>-1</sup>		
AC coil	I' D	2 "			5000h <sup>-1</sup>		
Operate/release			( D	-, -	Sms		
Bounce time ma		rm A/			Sms	wooh 1)	
			See ele	ectrical er	ndurance g	μαριτή	
Contact rating	Contact	Loac	1			Ouglas	
Type IEC 61810	Contact	Load				Cycles	
RT314 DC-coil	A (NO)	161	250VAC,	0000 1	0500	30x10 <sup>3</sup>	
RT314 DC-coil	C (CO)		250VAC,			10x10 <sup>3</sup>	
RT314 DC-coil	A (NO)		400VAC,			150x10 <sup>3</sup>	
RT114 DC-coil	A (NO)	,	250VAC,			50x10 <sup>3</sup>	
RT114 AC-coil	A (NO)	,	250VAC,			100x10 <sup>3</sup>	
UL 508	71(110)	12/1,	200 17 10,	σσσφ=1,	700	100010	
BT314	A/B (NO/NC)	20A	250VAC	general r	urpose, 85	5°C 6x10 <sup>3</sup>	
RT334	A (NO)	,			ose, 85°C		
RT314	A (NO)	,	240VAC.	0 1 1	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	1x10 <sup>3</sup>	
RT314	A (NO)	1- /	,		OVAC, 70°C		
EN60947-4-1	\··-/		.,	,			


250V/6A, AC-3

250V/2A, AC-3



RT314 DC-coil A (NO)

RT314 AC-coil A (NO)





E0144-C







## EN60947-5-1

100x10<sup>3</sup> RT314 DC-coil A (NO) 12(2)A, 250VAC, 85°C 1) For reflow solderable versions: actual contact performance may be influenced by the reflow soldering process.

Contact Data (continued)					
Mechanical endurance					
DC coil	>30x10 <sup>6</sup> operations				
AC coil	>10x10 <sup>6</sup> operations				
AC coil, reflow version	>5x10 <sup>6</sup> operations				

Coil Data	
Coil voltage range, DC coil/ AC coil	5 to 110VDC / 24 to 230VAC
Operative range, IEC 61810	2
Coil insulation system according UL	class F

#### Coil versions, DC coil

Coil	Rated	Operate	Release	Coil	Rated coil				
code	voltage	voltage	voltage	resistance	power				
	VDC	VDC	VDC	$\Omega \pm 10\%^{2)}$	mW				
005	5	3.5	0.5	62	403				
006	6	4.2	0.6	90	400				
009	9	6.3	0.9	200	400				
012	12	8.4	1.2	360	400				
018	18	12.6	1.8	770	420				
020	20	14.0	2.0	952	420				
024	24	16.8	2.4	1440	400				
048	48	33.6	4.8	5520	417				
060	60	42.0	6.0	8570 <sup>2)</sup>	420				
110	110	77.0	11.0	28800 <sup>2)</sup>	420				
0) 0 - :1 :-	0.000								

2) Coil resistance ±12%

6.050

6.050

All figures are given for coil without pre-energization, at ambient temperature  $+23^{\circ}\text{C}$ . Other coil voltages on request.

### Coil versions, AC coil 50/60 Hz


	,				
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VAC	VAC	VAC	$\Omega \pm 15\%^{(3)}$	VA
524	24	18.0	3.6	350 <sup>3)</sup>	0.76
615	115	86.3	17.3	8100	0.76
620	120	90.0	18.0	8800	0.75
700	200	150.0	30.0	24350	0.76
730	230	172.5	34.5	32500	0.74


3) Coil resistance ±10%

All figures are given for coil without pre-energization, at ambient temperature +23°C, 50 Hz. Other coil voltages on request.



# Power PCB Relay RT1 (Continued)





Insulation Data					
Initial dielectric strength					
between open contacts	1000V <sub>rms</sub>				
between contact and coil	5000V <sub>rms</sub>				
Clearance/creepage					
between contact and coil	≥10/10mm				
Material group of insulation parts	Illa				
Tracking index of relay base	PTI 250V				
reflow version	PTI 175V				

## **Other Data**

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter

Resistance to heat and fire

WG version or Reflow version according EN60335, par30

Ambient temperature

DC coil -40 to 85°C AC coil -40 to 70°C

Category of environmental protection, IEC 61810

RTII - flux proof, RTIII - wash tight standard version reflow version RTII - flux proof

Vibration resistance (functional)

form A/form B contact, 30 to 500Hz 20g/5g Shock resistance (destructive) 100g

#### Other Data (continued)

Terminal type standard version PCB-THT, plug-in reflow version PCB-THR Mounting distance AC coil: ≥2.5mm

Weight 14g Resistance to soldering heat THT, IEC 60068-2-20

270°C/10s RTII 260°C/5s

Resistance to soldering heat THR

reflow soldering (for reflow version) forced gas convection 4) or vapour phase  $^{5)}$ 

according EN61730 temperature profile Packaging/unit tube/20 pcs., box/500 pcs

4) infrared heating not allowed

5) recommended fluid LS/230


### **Accessories**

For details see datasheet Accessories Industrial Power Relay RT NOTE: indicated contact ratings and electrical endurance data for direct wiring of relays (according IEC 61810-1); for relays mounted on sockets deratings may apply.


# PCB layout / terminal assignment

Bottom view on solder pins

12A, pinning 3.5mm




12A, pinning 5mm





\*) With the recommended PCB hole sizes a grid pattern from 2.5mm to 2.54mm can be used.


16A, pinning 5mm





S0418-CA


















S0163-BG


S0163-BC




# Power PCB Relay RT1 (Continued)


#### **Dimensions**





**Process conditions for Reflow soldering** according to EN61760-1





Produc	ct code structure	Typical product code	RT	3	1	4	024
Гуре							
F	RT Power PCB Relay RT1						
Version							
1	I 12A, pinning 3.5mm, flux proof						
2	2 12A, pinning 5mm, flux proof *)						
3	3 16A, pinning 5mm, flux proof						
E	3 12A, pinning 3.5mm, wash tight						
	16A, pinning 5mm, wash tight						
Contact	arrangement						
1	1 form C (CO) contact						
3	3 1 form A (NO) contact						
Contact	material						
4	<b>I</b> AgNi 90/10						
5	AgNi 90/10 gold plated (for type RT31.)						
Coil		·					
	Coil code: please refer to coil versions table						
Version							
E	Blank Standard version						

WG Product in accordance with IEC 60335-1 (domestic appliances)

Reflow solderable R

\*) Wash tight version on request



# Power PCB Relay RT1 (Continued)

Product code	Version	Contacts	Contact material	Coil	Version	Part number
RT114009	12A, pinning 3.5mm,	1 form C (CO)	AgNi 90/10	9VDC	Standard	1393239-9
RT114012	flux proof	contact		12VDC		1419108-1
RT114012WG	·				IEC60335-1 compliant	7-1415538-6
RT114024				24VDC	Standard	1-1393239-3
RT114024WG					IEC60335-1 compliant	1415539-4
RT114730				230VAC	Standard	1-1393239-9
RT115024			AgNi 90/10 gold pl.	24VDC		2-1393239-1
RT134012		1 form A (NO)	AgNi 90/10	12VDC		2-1393239-6
RT134024		contact	, and the second	24VDC		3-1393239-0
RT214012	12A, pinning 5mm,	1 form C (CO)		12VDC		5-1393239-4
RT214024	flux proof	contact		24VDC		5-1393239-5
RT214524	·			24VAC		5-1393239-9
RT214730				230VAC		1419108-6
RT314005	16A, pinning 5mm,			5VDC		9-1393239-1
RT314006	flux proof			6VDC		9-1393239-3
RT314012	·			12VDC		9-1393239-5
RT314012WG					IEC60335-1 compliant	8-1415535-6
RT314018				18VDC	Standard	9-1393239-7
RT314024				24VDC		9-1393239-8
RT314024WG					IEC60335-1 compliant	1415538-7
RT314048				48VDC	Standard	1393240-1
RT314730				230VAC		1393240-7
RT315024			AqNi 90/10 gold pl.	24VDC		1-1393240-4
RT334009WG		1 form A (NO)	AgNi 90/10	9VDC	IEC60335-1 compliant	3-1415538-1
RT334012		contact		12VDC	Standard	4-1393240-5
RT334012WG					IEC60335-1 compliant	1-1415527-1
RT334024				24VDC	Standard	4-1393240-8
RT334048				48VDC		5-1393240-0
RTB14005	12A, pinning 3.5mm,	1 form C (CO)		5VDC		1-1393238-2
RTB14012	wash tight	contact		12VDC		1-1393238-5
RTB14024	3			24VDC		1-1393238-9
RTB14524				24VAC		2-1393238-4
RTD14005	16A, pinning 5mm,			5VDC		5-1393238-9
RTD14012	wash tight			12VDC		6-1393238-2
RTD14024				24VDC		6-1393238-8
RTD14048				48VAC		6-1393238-9