





## Modulo luminoso a led.

*Led luminous module.*

*Module lumineux à LED*

*LED-Lichtmodul*

*Módulo de luz LED*

<b>CUPOLA</b> DOME DOME HAUBE CÚPULA	PC								
<b>GHIERA</b> RING BAGUE RING CONTERA	PC								
<b>GRUPPO OTTICO</b> LUMINOUS SOURCE SOURCE LUMINEUSE LICHTQUELLE FUENTE DE LUZ	N°12 LED								
<b>COLORI DISPONIBILI</b> AVAILABLE COLOURS COULEURS DISPONIBLES VERFÜGBARE FARBEN COLORES DISPONIBLES									
<b>TENSIONE DI ALIMENTAZIONE</b> VOLTAGE TENSION SPANNUNG TENSIÓN	24 Vdc/Vac – 240Vac								
<b>SERVIZIO</b> OPERATION FONCTIONNEMENT BETRIEBSART FUNCIONAMIENTO	∞								
<b>CORRENTE NOMINALE</b> CURRENT CONSUMPTION CONSOMMATION DE COURANT STROMAUFNAHME CONSUMO DE CORRIENTE	<table border="1"> <thead> <tr> <th></th> <th>24 Vdc</th> <th>24 Vac</th> <th>240Vac</th> </tr> </thead> <tbody> <tr> <th>mA</th> <td>65</td> <td>85</td> <td>35</td> </tr> </tbody> </table>		24 Vdc	24 Vac	240Vac	mA	65	85	35
	24 Vdc	24 Vac	240Vac						
mA	65	85	35						
<b>RESA LUMINOSA</b> LIGHT OUTPUT RENDEMENT LUMINEUX LICHT LEISTUNG SALIDA DE LUZ									
<b>MODALITA' LUCE</b> LIGHT EFFECT EFFET LUMINEUX LICHTEFFEKT EFECTO LUMINOSO	Fissa Steady Fixe Dauerlicht Luz fija								
<b>GRADO IP</b> IP RATING DEGRE IP SCHUTZART GRADO IP	IP66								

<b>TEMPERATURA DI FUNZIONAMENTO</b> <i>OPERATING TEMPERATURE</i> <i>TEMPERATURE DE SERVICE BETRIEBSTEMPERATUR</i> <i>TEMPERATURA DE FUNCIONAMIENTO</i>	-30°C+50°C
<b>VIBRAZIONI</b> <i>VIBRATIONS</i> <i>VIBRATIONS</i> <i>VIBRATIONEN</i> <i>VIBRACIONES</i>	INDUSTRIAL CEI 60068-2-6 SINE
<b>CERTIFICAZIONI, OMOLOGAZIONI</b> <i>CERTIFICATIONS, APPROVALS CERTIFICACIONES,</i> <i>HOMOLOGATIONS PRODUKTZERTIFIKATE,</i> <i>ZULASSUNGEN CERTIFICADOS, HOMOLOGACIONES</i>	CE, UKCA
<b>FISSAGGIO</b> <i>MOUNTING</i> <i>FIXATION</i> <i>FIXIERUNG</i> <i>FIJACIÓN</i>	Tramite ghiera <i>Ring</i> <i>Bague</i> <i>Ring</i> <i>Contera</i>
<b>DISEGNO</b> <i>TECHNICAL DRAWING</i> <i>DESSIN</i> <i>TECHNISCHE ZEICHNUNG</i> <i>DIBUJO TECNICO</i>	