



213752
SBT-RGB-R50-3S-B5
Signal column

- Status display 360°
- Strong signal effect thanks to state-of-the art, high-efficiency LEDs
- Low energy consumption
- Can be used immediately thanks to three trigger inputs (eight predefined/user-defined color settings)
- Freely configurable functions via IO-Link (process data)
- Simple installation (M30 threading)



Legende / Legend:

- >RT< = Rot langsam blinkend / flashing red slowly
- >>RT<< = Rot blitzend / rapidly flashing red
- >BUZ< = Buzzer intermittierend / Buzzer intermittent (1Hz)
- >>BUZ<< = Buzzer intermittierend / Buzzer intermittent (2,5Hz)

All Trigger Inputs have a delay ~50 ms.
Pre-sets can be defined via IO-Link.

TRIG 1	TRIG 2	TRIG 3	Pre-Set	Factory setting (Seg 1 / Seg 2 / Seg 3 / BUZ)					
				Var. 3S			Var. 3B		
0	0	0	1	--	--	--	--	--	--
1	0	0	2	--	--	RT	--	--	RT
0	1	0	3	GN	--	--	GN	--	--
1	1	0	4	--	YE	--	--	YE	--
0	0	1	5	BU	--	--	BU	--	--
1	0	1	6	WH	--	--	WH	--	--
0	1	1	7	--	--	>RT<	--	--	>BUZ<
1	1	1	8	--	--	>>RT<<	--	--	>>BUZ<<

BK: black
BN: brown
BU: blue
GN: green
GY: grey
WH: white
YE: yellow

Function										

Technical data (typ.)	+20°C, 24 V DC
Service voltage	18 ... 30 V DC (Supply Class 2)
Internal power consumption	175 mA (24 V DC)
Power	4,2 W (24 V)
Inverse polarity protection	Yes
Illuminated area	50 x 37 mm (Ø x H / segment)
Dimensions of luminaire unit (Ø x H)	Ø 50,6 x 165 mm
Number of segments	3
Housing material	Aluminum (natural, Anodized)
Material	Polycarbonate (Diffusor)
Weight	270 g
Protection class	III, operation on protective low voltage
Risk group (DIN EN 62471)	Free group
Model	Signal column
Operating modes	External trigger / segment mode / level mode / demo mode, LED operating modes: Static / Blinking / Flashing
Color selection	Red, green, yellow, blue, white, orange, pink, user-defined
Light intensity can be adjusted	10 to 100 %, via IO-Link
Trigger input high level	> 8,0 V
Trigger input low level	< 5,0 V

**213752****SBT-RGB-R50-3S-B5****Signal column****Technical data (typ.)****+20°C, 24 V DC**

Trigger input

8 color presets: selectable via trigger 1 + 2 +3

Interface

- IO-Link (V1.1, COM2 38,4 kBd, 5 000 µs)
- for parameterization (process data)

Color

RGB

Vibration load

10 ... 55 Hz / 0,35 mm

Ambient temperature during operation

0 ... +50 °C

Protection type

IP 65

Connection

Connector, M12, 5-pin

Connection cable

VK ... /5-SB

More information / accessories<https://www.di-soric.com/213752>