

proximity sensor


SDBT-MSX-1L-NU-E-5-N-LE

Part number: 8059125

★ Core product range

New


FESTO



[PDF](#) General operating conditions

[PDF](#) Data sheet

→ Datasheet product reliability



Data sheet

Feature	Value
Shipping date	→ View
Design	for T-slot
Based on the standard	EN 60947-5-2
Authorisation	RCM Mark
CE mark (see declaration of conformity)	to EU directive for EMC in accordance with EU RoHS directive
KC mark	KC-EMV
Materials note	Free of copper and PTFE Conforms to RoHS Halogen-free
Measured variable	Position
Measuring principle	Hall magnetic
Ambient temperature	-40 ... 85 °C
Max. travel speed	3 m/s
Repetition accuracy	0.1 mm
Switch output	PNP/NPN, switchable
Switching element function	Normally open contact
Hysteresis	0.2 mm
Switch-on time	≤ 2 ms
Switch-off time	≤ 2 ms
Max. switching frequency	200 Hz
Max. output current	100 mA
Max. output current in mounting kits	100 mA
Max. contact rating DC	2.8 W
Max. switching capacity DC in mounting kits	2.8 W
Voltage drop	< 1.5 V
Minimum load current	0.15 mA
Residual current	< 0.2 mA
Short circuit strength	Yes
Overload withstand capability	Available
Nominal operating voltage DC	24 V
Operating voltage range DC	10 ... 30 V
Polarity protected	for all electrical connections
Electrical connection 1, connection type	Cable
Electrical connection 1, connection technology	Open end
Electrical connection 1, number of pins/wires	3
Connector exit direction	axial
Test conditions of cable	Bending strength according to Festo standard Test conditions on request Chain link trunking: 5 million cycles, bending radius 28 mm Torsion resistance: > 300,000 cycles, ±270°/0.1 m
Cable length	5 m
Cable attribute	Energy chain + robot
Cable sheath colour	Grey
Material cable sheath	TPE-U(PUR)
Wire ends	Wire end ferrule
Mounting type	Tightened Insertable in slot from above
Max. tightening torque	0.6 Nm
Assembly position	Any
Product weight	56 g

Feature	Value
Housing colour	Black
Material housing	PA-reinforced High alloy steel, non-corrosive
Operating status display	Yellow LED
Status display	Green LED
Setting options	Auto Teach-In Capacitive pushbutton
Ambient temperature with flexible cable installation	-5 ... 85 °C
Protection class	IP68