SFH 4780S

OSLUX®

IR OSLUX (810nm) - 20°







Applications

Access Control / Biometrics (IRIS, Scan, Vein scan)

Features:

- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)
- IR lightsource with high efficiency
- Double stack emitter
- Low thermal resistance (Max. 25 K/W)
- Centroid wavelength 810 nm
- Narrow half angle (± 10°)

Ordering Information

Туре	Radiant intensity 1)	Radiant intensity 1) typ.	Ordering Code
	$I_{\rm F} = 1 \text{ A}; t_{\rm p} = 10 \text{ ms}$ $I_{\rm e}$	$I_{\rm F} = 1 \text{ A}; t_{\rm p} = 10 \text{ ms}$ $I_{\rm e}$	
SFH 4780S	2200 4400 mW/sr	2900 mW/sr	Q65111A6054



Maximum Ratings

$T_{\scriptscriptstyle \wedge}$	=	25	$^{\circ}C$
* A			_

Parameter	Symbol		Values
Operating temperature	T _{op}	min. max.	-40 °C 85 °C
Storage temperature	T_{stg}	min. max.	-40 °C 85 °C
Junction temperature	T _j	max.	145 °C
Forward current	I _F	max.	500 mA
Surge current $t_p \le 200 \mu s; D = 0$	I _{FSM}	max.	2 A
Reverse current ²⁾	I _R	max.	200 mA
Power consumption	P _{tot}	max.	1.8 W
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)	V_{ESD}	max.	2 kV

For the forward current and power consumption please see "maximum permissible forward current" diagram



Characteristics


 $I_{\scriptscriptstyle F}$ = 1000 mA; $t_{\scriptscriptstyle p}$ = 10 ms; $T_{\scriptscriptstyle A}$ = 25 °C

Parameter	Symbol		Values
Peak wavelength	∖ peak	typ.	820 nm
Centroid wavelength	$\lambda_{ m centroid}$	typ.	810 nm
Spectral bandwidth at 50% I _{rel,max}	Δλ	typ.	30 nm
Half angle	φ	typ.	10 °
Dimensions of active chip area	LxW	typ.	0.75 x 0.75 mm x mm
Rise time (10% / 90%) $I_F = 1 \text{ A}; R_L = 50 \Omega$	t,	typ.	8 ns
Fall time (10% / 90%) $I_F = 1 \text{ A}; R_L = 50 \Omega$	t _f	typ.	14 ns
Forward voltage $I_F = 0.5 \text{ A}$; $t_p = 100 \mu\text{s}$	V_{F}	typ. max.	3.3 V 3.6 V
Forward voltage $I_F = 1 \text{ A}$; $t_p = 100 \mu\text{s}$	V_{F}	typ.	3.6 V
Reverse voltage ²⁾ I _R = 20 mA	V_R	max.	1.2 V
Reverse voltage (ESD device) 2)	V_{RESD}	min.	45 V
Total radiant flux 3)	Фе	typ.	600 mW
Total radiant flux $^{3)}$ I _F = 1 A; t _p = 100 µs	Фе	typ.	680 mW
Temperature coefficient of brightness	TC _I	typ.	-0.3 % / K
Temperature coefficient of voltage	TC_{v}	typ.	-2 mV / K
Temperature coefficient of wavelength	TC _λ	typ.	0.3 nm / K
Thermal resistance junction solder point real 4)	R_{thJS}	max.	25 K / W




Relative Spectral Emission 5), 6)

 $I_{rel} = f(\lambda); I_F = 1000 \text{ mA}; t_p = 10 \text{ ms}$




Radiation Characteristics 5), 6)

 $I_{rel} = f(\phi)$




Forward current 5), 6)

 $I_F = f(V_F)$; single pulse; $t_D = 100 \mu s$




Relative Radiant Intensity 5), 6)

 $I_e/I_e(1A) = f(I_F)$; single pulse; $t_p = 100 \mu s$




Max. Permissible Forward Current

$$I_{F,max} = f(T_S); R_{thJS} = 25 K/W$$




Permissible Pulse Handling Capability

 $I_{\scriptscriptstyle F}$ = f (t_D); duty cycle D = parameter; $T_{\scriptscriptstyle A}$ = 85°C




Dimensional Drawing 7)



Approximate Weight: 40.0 mg **Package marking:** Cathode


ESD advice: LED is protected by ESD device which is connected in parallel to LED-Chip.

Recommended Solder Pad 7)



Reflow Soldering Profile

Product complies to MSL Level 3 acc. to JEDEC J-STD-020E






SFH 4780S

Profile Feature	Symbol	Pb	-Free (SnAgCu) Ass	sembly	Unit
	·	Minimum	Recommendation	Maximum	
Ramp-up rate to preheat*) 25 °C to 150 °C			2	3	K/s
Time t_s T_{Smin} to T_{Smax}	t _s	60	100	120	S
Ramp-up rate to peak*) T_{Smax} to T_{P}			2	3	K/s
Liquidus temperature	T_{L}		217		°C
Time above liquidus temperature	$t_{\scriptscriptstyle L}$		80	100	S
Peak temperature	T _P		245	260	°C
Time within 5 °C of the specified peak temperature T _P - 5 K	t _P	10	20	30	S
Ramp-down rate* T _p to 100 °C			3	6	K/s
Time 25 °C to T _P				480	S

All temperatures refer to the center of the package, measured on the top of the component

Taping 7)




C63062-A4242-B1-03



^{*} slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range

Tape and Reel 8)



Reel dimensions [mm]


A	W	N_{min}	W_1	$W_{2 \text{max}}$	Pieces per PU
330 mm	12 + 0.3 / - 0.1	60	12.4 + 2	18.4	2500



Barcode-Product-Label (BPL)




Dry Packing Process and Materials 7)



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.



Transportation Packing and Materials 7)



Dimensions of transportation box in mm

Width	Length	Height
349 ± 5 mm	349 ± 5 mm	33 ± 5 mm



Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the LED specified in this data sheet fall into the class **exempt group (exposure time 10000 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

For further application related informations please visit www.osram-os.com/appnotes



Disclaimer

Disclaimer

Language english will prevail in case of any discrepancies or deviations between the two language wordings.

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version in the OSRAM OS Webside.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest

By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product safety devices/applications or medical devices/applications

OSRAM OS components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

In case Buyer - or Customer supplied by Buyer- considers using OSRAM OS components in product safety devices/applications or medical devices/applications, Buyer and/or Customer has to inform the local sales partner of OSRAM OS immediately and OSRAM OS and Buyer and /or Customer will analyze and coordinate the customer-specific request between OSRAM OS and Buyer and/or Customer.



Glossary

- Radiant intensity: Measured at a solid angle of $\Omega = 0.001 \text{ sr}$
- Reverse Operation: Reverse Operation of 10 hours is permissible in total. Continuous reverse operation is not allowed.
- Total radiant flux: Measured with integrating sphere.
- Thermal resistance: junction soldering point, of the device only, mounted on an ideal heatsink (e.g. metal block)
- Typical Values: Due to the special conditions of the manufacturing processes of LED, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- Testing temperature: $T_{\Delta} = 25^{\circ}C$
- Tolerance of Measure: Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.
- ⁸⁾ **Tape and Reel**: All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.



Published by OSRAM Opto Semiconductors GmbH EU RoHS and China RoHS compliant product Leibnizstraße 4, D-93055 Regensburg www.osram-os.com © All Rights Reserved.

此产品符合欧盟 RoHS 指令的要求; 按照中国的相关法规和标准,不含有毒有害物质或元素。

