

ROLINE Gigabit Ethernet Industrial Switch, 8x RJ45

Product No.	21.13.1161
Manufacturer	ROLINE
Manufacturer No.	21.13.1161
EAN (single piece)	7611990117413



Network switch for use in a industrial environment

- Provides 8x 10/100/1000Mbps copper ports
- Auto-negotiation
- Auto MDI/MDI-X crossover function
- Supports IEEE 802.3x flow control for full duplex
- Supports back pressure flow control for half duplex
- Fully non-blocking Gigabit full wire speed switching performance
- Jumbo frame support
- Operating Power: +5 to +30VDC
- Alarm relay output for power failure event and configured port link fault events
- Wide operating temperature range
- Supports Green Ethernet power saving
- Entry DC by clamp or DC-powerconnector (6,3mm/2,0mm)
- Supports IEEE 802.3az Energy Efficient Ethernet
- Supports DIN-Rail mounting and panel mounting
- As PSU we recommend 21.13.1226
- Industrial-rated emission and immunity performance

Technical specifications

Manufacturer	ROLINE
Product group	Network Switches
Product type	Gigabit Ethernet Switch

Colour	black
Scope of delivery	Switch
Network standard	Gigabit Ethernet
LAN (Mbps)	10/100/1000
Quantity of ports	8
Gigabit Ethernet Ports RJ-45	8
Mounting form	DIN Rail
Stackable	No
Dimensions (HxWxD)	42 x 106 x 140 mm
Power supply unit (internal/external)	External