

SA110S-XX

10W/12W Switching Adapter

ı	n	b	u	1
•		r	ч	

Rated Voltage 100 - 240 VAC Max. Voltage 90 - 264 VAC Line Frequency 47 - 63 Hz

Current 300mA at 100-240VAC

Configuration Interchangeable

Output

Model Name	Voltage	Current	Watt	Efficiency
SA110S-05	5V	2A	10W	75%
SA110S-09	9V	1.2A	10.8W	80%
SA110S-12	12V	1A	12W	80%

Line Regulation Less than ±2% Load Regulation Less than ±5%

Protections OCP, OVP & Short circuit

Ripple & Noise \leq 100mVp-p,

Electrical

Topology Switching Mode

Hi-Pot 3000 Vac/1sec @ 5mA

(primary - secondary)

Leakage Current ≤0.25mA,at 264VAC/50Hz

Hold Up Time ≥8 mSec Standby Power ≤0.075 Watt

EMI Complies with EMI directives

product complies with EU (Efficiency Level Tier 2 - 2016)

CEC Requirement Efficiency Level: VI

Mechanical

Case Size 63L x 48W x 37H mm

Case Material Black, 94V-1 or equivalent

Weight (ref.) 100, ±10 g DC Cord 4.92ft

Environment

Operating Temp. 0°C - 40°C

Storage Temp. -20°℃ - 80°℃

10% - 90% (Non-condensing) Humidity

RoHS & WEEE Standard








SAA


VDE













Reliability

MTBF 50,000 hrs (by MIL-217 Standard) Safety ITE: UL,cUL,TUV/GS,CE,CB

Others

Package 100 pcs/box Min. Order 1K pcs/lot Warranty 1 year

For reference only. For details please contact your

local sales representative

SINO-AMERICAN ELECTRONICS CO., LTD 305 YU-LIN RD, CHIO-TOU, KAOHSIUNG CITY, TAIWAN

TEL: 886-7-6116156~9; FAX: 886-7-6116006

http://www.sac.com.tw