

Features



- Clear set
- Easy to handle
- 60 values per set
- E12 from 10 Ω up to 1M including 0 Ω, excluding 12 Ω and 820 K
- Standard rectangular thick film chip resistors produced by Vishay and Yageo

Variants

SMD-RCL 25

25 resistors per value

SMD-RCL 50

50 resistors per value

SMD-RCL 100

100 resistors per value

Electrical specifications

Dimensions (L x W)

0603 (in inch), 1608 (in mm)

Tolerance

± 1%

Temperature coefficient

± 100 ppm/K

Rated dissipation

0.10 W @ 70°C


Maximum voltage

75 V \leq

Values in the sets


0 Ω	33 Ω	100 Ω	330 Ω	1 K	3.3 K	10 K	33 K	100K	330K
10 Ω	39 Ω	120 Ω	390 Ω	1.2 K	3.9 K	12 K	39 K	120K	390K
15 Ω	47 Ω	150 Ω	470 Ω	1.5 K	4.7 K	15 K	47 K	150K	470K
18 Ω	56 Ω	180 Ω	560 Ω	1.8 K	5.6 K	18 K	56 K	180K	560K
22 Ω	68 Ω	220 Ω	680 Ω	2.2 K	6.8 K	22 K	68 K	220K	680K
27 Ω	82 Ω	270 Ω	820 Ω	2.7 K	8.2 K	27 K	82 K	270K	1M

Dimensions of the resistor



Dimensions [in mm]				
L	W	H	T1	T2
1.55 + 0.10 - 0.05	0.85 + 0.1 - 0.1	0.45 + 0.05 - 0.05	0.3 + 0.2 - 0.2	0.3 + 0.2 - 0.2

Dimensions of the pads



Dimensions [in mm]					
Reflow			Wave		
a	b	l	a	b	l
0.5	0.9	1.0	0.9	0.9	1.0

Constructiva AG

Schindellegistrasse 14, 8808 Pfäffikon, Switzerland

Phone +41 55 420 18 65, Fax +41 55 420 18 66

www.constructiva.ch

office@constructiva.ch