

Features

- Dry battery shape
- Low ESR
- Over 1,000,000 duty cycles


Applications

- UPS and backup power supply
- Electronic tools and police flash lights





Dimensions



Part Number	Dimension/ mm			
Fait Number	D	L		
SCE0450C0-0002R7TCZ	30.6	75.9		
SCE0700C0-0002R7TCZ	30.6	128.9		

Specifications

Items	Characteristics			
Operating Voltage	2.7 VDC			
Surge Voltage	2.85 VDC			
Operating Temperature Range	-40°C to 65°C			
Capacitance Tolerance	-10% to +20% (25°C)			
Temperature Performance(-40°C to 65°C)	$\Delta C \le 5\%$ of initial measured value@ 25°C ESR $\le 150\%$ of specified value			
Life (1500 hours @ 65°C, 2.7 VDC)	$\Delta C \le 20\%$ of initial measured value ESR $\le 200\%$ of specified value $\Delta C \le 20\%$ of initial measured value ESR $\le 200\%$ of specified value			
Cycle life (1,000,000 cycles between V_R and 1/2 V_R)				

Standard Product

	CAP (F)	Part Number	ESR (ı	(mohm) LC	Max.	Max.	Max.	Max.	Typical Thermal	Typical	Typical	
			AC @ 1kHz	DC	(mA, RT 72hrs)	Stored Der	Density (Wh/Kg)		Peak Current (A)	Resistance (Housing) °C /W	Thermal Capacitance, C _{th} , J/°C	Mass (g)
	450	SCE0450C0- 0002R7TCZ	9	12	1.5	0.46	5.8	8/13	95	19.5	85	78
-	700	SCE0700C0- 0002R7TCZ	2	3	1.6	0.71	5.8	26/43	305	7.4	140	123

Web: www.spscap.com Tel: +86-400-600-7891 Fax: +86-10-61272268 Email: info@spscap.com